284065-2 ✔ ACTIVE


Buchanan

TE Internal #: 284065-2

PCB Terminal Blocks, Header, Wire-to-Board, 2 Position, 5.08mm [.2in] Centerline, 2 Row, 30 – 12AWG Wire Size, .05 – 3mm² Wire Size

View on TE.com >

Connectors > Terminal Blocks & Strips > PCB Terminal Blocks







Terminal Block Connector Type: **Header**

Connector System: **Wire-to-Board**

Number of Positions: **2**

Centerline (Pitch): **5.08 mm [.2 in]**

Number of Rows: **2**

Features

Product Type Features

Block Type	PCB Mount
Header Type	Shrouded
Terminal Block Connector Type	Header
Connector System	Wire-to-Board
Connector & Contact Terminates To	Printed Circuit Board

Configuration Features

Threaded Flange	Without
Closed End	With
Number of Positions	2
Number of Rows	2

Electrical Characteristics

Current Rating (Max)	15 A
Voltage Rating	300 VAC

Body Features

Interlock	With

Contact Features

Contact Mating Area Plating Material	Tin
Contact Mount	Through Hole
Contact Base Material	Brass
Contact Current Rating (Max)	15 A

Mechanical Attachment

Screwless Terminal Block	Yes
Mounting Angle	Vertical
Screw Flange	Without
Connector Mounting Type	Board Mount

Housing Features

Housing Color	Green
Housing Material	PA 66
Centerline (Pitch)	5.08 mm[.2 in]

Dimensions

PCB Tail Length	3.5 mm[.138 in]
Wire Size	.05 – 3 mm²

Usage Conditions

Operating Temperature Range	-40 – 105 °C[-40 – 221 °F]

Operation/Application

Circuit Application	Power & Signal

Packaging Features

Packaging Method	Box
Packaging Quantity	300

Product Compliance

For compliance documentation, visit the product page on TE.com>


EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	

	Current ECHA Candidate List: JAN 2021 (211) Candidate List Declared Against: JUN 2020 (209) SVHC > Threshold: Not Yet Reviewed
Halogen Content	Not Yet Reviewed for halogen content
Solder Process Capability	Wave solder capable to 240°C


Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: https://echa.europa.eu/guidance-documents/guidance-on-reach


Compatible Parts



TE Part # 796634-2
2 POS 5.08MM R/A PLUG,TRM BLK




TE Part # 284041-2
TERMINAL BLOCK VERTICAL PLUG S




TE Part # 282807-2
TERMI-BLOK PLUG STACKING 2P5,




TE Part # 796635-2
2 POS 5.08MM R/A PLUG,TRM BLK




TE Part # 284047-2
TERMI-BLOK VERTICAL PLUG STACK



TE Part # 1776165-2
2P TERMI-BLOK HDR,HIGH TEMP



TE Part # 1986262-2
2 POS PLUG SPRING CONN, PITCH 5.08



TE Part # 5-796634-6
TERMI-BLOK HDR,-2 W/8MICRO" AU

Customers Also Bought




TE Part #1-2271656-1
Mini I/O Straight Header Type 1



TE Part #1734290-2
IEEE 1394, RCPT, 6P, V/T, DIP, H 3.18



TE Part #2-178216-2
DYNAMIC 3400F HDR ASSY



TE Part #900412-1
PC I/O RETENTION LEG ASSY 80P



TE Part #2-2013519-0
DYNAMIC D3900 H-HDR ASSY 10P Y TYPE-A



TE Part #3-2134249-3
D3900S 7.5MM PITCH REC ASSY 3P BLACK Z



TE Part #3-5175475-5
CHAMP 050 B/B REC V W/LEG 40P



TE Part #2-87025-5
02 MODI CRMP S-I HSG SR .156CL



TE Part #2352424-1
REC Contact 3 Series Reel, MMC-PB

Documents

Product Drawings

TERMI-BLOK HDR 180, 5.08MM P.M

English

CAD Files

Customer View Model

ENG_CVM_284065-2_C.3d_igs.zip

English

Customer View Model

ENG_CVM_284065-2_C.3d_stp.zip

English

Customer View Model

ENG_CVM_284065-2_C.2d_dxf.zip

English

3D PDF

English

By downloading the CAD file I accept and agree to the Terms and Conditions of use.

Datasheets & Catalog Pages

Eurostyle Terminal Blocks Focus Product Stock List

English

BUCHANAN TERMINAL BLOCKS CATALOG - EUROSTYLE TERMINAL BLOCKS

English

1-1773458-1_EURO_STYLE_TERMINAL_BLOCKS_QRG

English

Product Specifications

Application Specification

English