284507-5 ✔ ACTIVE


Buchanan

TE Internal #: 284507-5

PCB Terminal Blocks, Plug, Wire-to-Board, 5 Position, 3.81mm [.15in] Centerline, 1 Row, Side Wire Entry Angle, 30 – 14AWG Wire Size

View on TE.com >

Connectors > Terminal Blocks & Strips > PCB Terminal Blocks



Terminal Block Connector Type: **Plug**

Connector System: **Wire-to-Board**

Number of Positions: **5**

Centerline (Pitch): **3.81 mm [.15 in]**

Number of Rows: **1**

Features

Product Type Features

Wire Protection	With
Block Type	Stacking Plug
Terminal Block Connector Type	Plug
Connector System	Wire-to-Board
Connector & Contact Terminates To	Wire & Cable

Configuration Features

Stacking Configuration	Side Stackable
Number of Positions	5
Number of Rows	1
Wire Entry Angle	Side

Electrical Characteristics

Current Rating (Max)	11 A
Voltage Rating	300 VAC

Body Features

Interlock	Without

Contact Features

Contact Mating Area Plating Material	Tin
Contact Base Material	Phosphor Bronze
Contact Current Rating (Max)	11 A

Mechanical Attachment

Screwless Terminal Block	No
Mounting Angle	Right Angle
Screw Size	M2
Screw Plating Material	Nickel
Screw Material	Brass
Screw Flange	Without

Housing Features

Housing Color	Green
Housing Material	PA 66
Centerline (Pitch)	3.81 mm[.15 in]

Dimensions

Wire Size	.05 – 2 mm²

Usage Conditions

Operating Temperature Range	-40 – 105 °C[-40 – 221 °F]

Operation/Application

Circuit Application	Power & Signal

Packaging Features

Packaging Quantity	150

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant with Exemptions
EU ELV Directive 2000/53/EC	Compliant with Exemptions
China RoHS 2 Directive MIIT Order No 32, 2016	Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2021 (211)

	Candidate List Declared Against: JAN 2020 (205) SVHC > Threshold: Not Yet Reviewed
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: https://echa.europa.eu/guidance-documents/guidance-on-reach

Compatible Parts



TE Part # 2342071-5
5POS HDR ST,HT, 3.5MM PITCH, TL 1.9MM




TE Part # 2342076-5
5POS HDR 90 DEG,HT,3.5MM PITCH, TL 1.9MM




TE Part # 2342077-5
5POS HDR 90 DEG,HT,3.81MM PITCH, TL 1.9MM




TE Part # 2342078-5
5POS HDR ST, HT, 3.81MM PITCH, TL 1.9MM




TE Part # 284517-5
5P TERMIBLOK HDR DIR POL



TE Part # 284513-5
5 POS TERMI-BLOK HDR 900 POL.



TE Part # 1776135-5
5P TERMI-BLOK HDR,HIGH TEMP



TE Part # 284518-5
5P TERMIBLOK HDR DIR MODULE

TE Part # 1-1986343-5
15P HDR CLOSED END,90 DEG,CL 3.81,BLK

Customers Also Bought



TE Part #1-50871-3
Mini Spring Sockets: Closed Bottom, 7.5A




TE Part #1-292173-2
AMP COMMON TERMINATION HEADERS




TE Part #1735446-7
AMP HPI 2.0MM HEADERS




TE Part #102694-3
10 AMPMODU MT ASSY DR .100CL



TE Part #2029150-5
5P R/A HDR VAL-U-LOK V2 W/P




TE Part #2-647123-6
06P MTA156 SHRD HDR ASSY SQ SN



TE Part #2-647123-3
03P MTA156 SHRD HDR ASSY SQ SN



TE Part #103634-2
03 MTE HDR SRRA LATCH .100CL



TE Part #2-535541-8
30 MODIV VRT SR CE 100/115

TE Part #YAFD57-12-3SNC1270
PLUG ASSY

Documents

Product Drawings

5 POS TERMI-BLOK PLUG STAC 3,8

English

CAD Files

Customer View Model

ENG_CVM_284507-5_C.3d_igs.zip

English

Customer View Model

ENG_CVM_284507-5_C.3d_stp.zip

English

Customer View Model

ENG_CVM_284507-5_C.2d_dxf.zip

English

3D PDF

English

By downloading the CAD file I accept and agree to the Terms and Conditions of use.

Datasheets & Catalog Pages

Eurostyle Terminal Blocks Focus Product Stock List

English

BUCHANAN TERMINAL BLOCKS CATALOG - EUROSTYLE TERMINAL BLOCKS

English

1-1773458-1_EURO_STYLE_TERMINAL_BLOCKS_QRG

English

Product Specifications

Application Specification

English