



Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2021 (211) Candidate List Declared Against: JAN 2021 (211) Does not contain REACH SVHC
Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Customers Also Bought



TE Part #1-179958-2
DYNAMIC 5000 REC AND TAB HSG



TE Part #1461353-6
PCFN SOLAR RELAY



TE Part #1-1827863-0
DYNAMIC 1100 REC AND TAB HSG



TE Part #1-770858-0
10P MINI UMNL HDR ASSY SNDBL L



TE Part #1-178314-5
DYNAMIC 3100 HDR ASSY

TE Part #1440007-2
STD OEG Miniature PCB OJ/OJE Pow Relays

TE Part #1-175196-2
DYNAMIC 3000 CONTACT

TE Part #153210-2
3 M/M LANCED PIN

TE Part #EKB001N00310001000
615 EXTENSION

Documents

Product Drawings
AMP OPTIMATE PN CONN

English

CAD Files
3D PDF

3D

Customer View Model
ENG_CVM_CVM_1123445-1_B.2d_dxf.zip

English

Customer View Model
ENG_CVM_CVM_1123445-1_B.3d_igs.zip

English

Customer View Model
ENG_CVM_CVM_1123445-1_B.3d_stp.zip

English

By downloading the CAD file I accept and agree to the Terms and Conditions of use.

Product Specifications
Assembly of AMP Optimate PN Connector

English

Application Specification
English