



Connectors > Lighting Connectors > Plug & Socket Connectors



Connector System: **Cable-to-Cable**
Number of Positions: **2**
Sealable: **No**
Connector & Contact Terminates To: **Wire & Cable**
Lighting Connector Style: **Splitter**

Features

Product Type Features

Product Type	Connector
Connector System	Cable-to-Cable
Sealable	No
Connector & Contact Terminates To	Wire & Cable
Lighting Connector Style	Splitter

Configuration Features

Keying Arrangement	HV-5
Number of Positions	2
Contacts Preloaded	No

Electrical Characteristics

Operating Voltage	42 VDC
-------------------	--------

Mechanical Attachment

Connector Mounting Type	Cable Mount (Free-Hanging)
-------------------------	----------------------------

Housing Features

Housing Color	White
---------------	-------

Operation/Application

Circuit Application	Power
---------------------	-------



Other

Comment	Parallel
---------	----------

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Not Yet Reviewed
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2021 (211) Candidate List Declared Against: JAN 2017 (173) SVHC > Threshold: Not Yet Reviewed
Halogen Content	Not Yet Reviewed for halogen content
Solder Process Capability	Not reviewed for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulations, TE’s information on SVHC in articles for this part number is still based on the European Chemical Agency (ECHA) ‘Guidance on requirements for substances in articles’(Version: 2, April 2011), applying the 0.1% weight on weight concentration threshold at the finished product level. TE is aware of the European Court of Justice ruling of September 10th, 2015 also known as O5A (Once An Article Always An Article) stating that, in case of ‘complex object’, the threshold for a SVHC must be applied to both the product as a whole and simultaneously to each of the articles forming part of its composition. TE has evaluated this ruling based on the new ECHA “Guidance on requirements for substances in articles” (June 2017, version 4.0) and will be updating its statements accordingly.

Compatible Parts



TE Part # 293234-1
NECTOR S T SPLITTER



Also in the Series

NECTOR S

Insertion & Extraction Tools(3)	Lighting Cable Assemblies(1)	Plug & Socket Lighting Connector Accessories(57)	Plug & Socket Lighting Connectors(54)

Customers Also Bought

TE Part #5-103945-9 2X10 MTE SHRD PIN SR LTCH .100	TE Part #3-644893-4 04P CST100 SHRD HDR ASSY LF	TE Part #485893-8 010 HOUSING FFC PIN 100CL SR	TE Part #5-103945-7 2X8 MTE SHRD PIN SR LATCH .100
TE Part #770983-1 .062 COMM P&S PIN 18-24 PTPBR	TE Part #293234-8 NECTOR S T SPLITTER LV-2	TE Part #293650-4 NECTOR S T-SPLITTER STANDARD	TE Part #3-644893-2 02P CST100 SHRD HDR ASSY LF
TE Part #293387-4 NECTOR S OUTLET LV-2 WHITE	TE Part #293388-5 NECTOR S PLUG LV-2 WHITE		

Documents

Product Drawings

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_293650-3_B.2d_dxf.zip



English

Customer View Model

[ENG_CVM_CVM_293650-3_B.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_293650-3_B.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

[NECTOR_S_LINE_CONNECTOR_BROCHURE](#)

English

Agency Approvals

[UL Report](#)

English