




Connectors > Rectangular Connectors > Rectangular Connector Accessories > Rectangular Backshells & Clamps



Backshell & Clamp Accessory Type: **Cable Gland**

Sealable: **Yes**

Features

Product Type Features

Backshell & Clamp Accessory Type	Cable Gland
Sealable	Yes

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant with Exemptions
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2021 (211) Candidate List Declared Against: JAN 2021 (211) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not reviewed for solder process capability


Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent



chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

 TE Part # T1220100125-000 H10B-TG-M25	 TE Part # T2020002002-000 CDF-0.3	 TE Part # T1210100225-000 H10B-TS-2M25	 TE Part # T1950240225-000 H24BPR-SGRH-2TM25
 TE Part # T1950240325-000 H24BPR-SGRH-3TM25	 TE Part # T3165250111-000 BLIND-25-M	 TE Part # T3165250111-100 BLIND-25-M-BX	 TE Part # T3161250050-000 LN-25-M

Customers Also Bought

 TE Part #T1230240132-000 H24B-TSH-M32	 TE Part #T1010242100-000 H24B-KDBP	 TE Part #T1230240125-000 H24B-TSH-M25	 TE Part #T1230240140-000 H24B-TSH-M40
 TE Part #T1240100132-000 H10B-TGH-M32	 TE Part #T1319100120-000 H10A-TS-M20	 TE Part #T3609400112-000 DLX-40-MT	 TE Part #T1010101200-000 H10B-KDTP



Documents

Product Drawings

DLX-25-MT

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_T3609250112-000_A.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_T3609250112-000_A.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_T3609250112-000_A.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

HEAVY DUTY CONNECTORS

English

Product Specifications

Application Specification

English

Product Environmental Compliance

TE Material Declaration

English