



Connectors > D-Shaped Connectors > D-Sub Connectors > Crimp D-Sub Connectors > D-Sub Crimp: Plug, Signal, 62 Posn, Pin Size 22, Shell Size 4



Connector & Housing Type: **Plug**

Connector System: **Cable-to-Cable**

Number of Positions: **62**

D-Sub Contact Size: **22**

D-Sub Shell Size: **4**

[All D-Sub Crimp: Plug, Signal, 62 Posn, Pin Size 22, Shell Size 4 \(4\)](#)

Features

Product Type Features

Grounding Indents	With
Product Type	Connector
Grade	Standard
Shell Type	Full Metal Shell
Connector & Housing Type	Plug
Connector System	Cable-to-Cable
D-Sub Shell Size	4
Sealable	No
Connector & Contact Terminates To	Wire & Cable

Configuration Features

Number of Positions	62
---------------------	----

Body Features

Shell Plating Material	Tin
Shield Plating Material	Tin
Shell Material	Steel
Shield Material	Steel
Insert Material	Nylon



Contact Features

D-Sub Contact Size	22
--------------------	----

Mechanical Attachment

Mating Retention	With
Mating Retention Type	4-40 Screwlock

Housing Features

Centerline (Pitch)	2.41 mm[.095 in]
--------------------	------------------

Dimensions

Cable Insulation Diameter Range	8.59 – 14.28 mm
---------------------------------	-----------------

Usage Conditions

Operating Temperature Range	-55 – 105 °C[-67 – 221 °F]
-----------------------------	----------------------------

Operation/Application

Shielded	Yes
Circuit Application	Signal

Industry Standards

Insert Flammability Rating	UL 94V-0
UL Flammability Rating	UL 94V-0

Packaging Features

Packaging Quantity	1
Packaging Method	Kit, Package

Other

Comment	Components shipped unassembled, each part bulk-packaged.
---------	--

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2021 (211) Candidate List Declared Against: JUN 2020 (209)



SVHC > Threshold:
Not Yet Reviewed

Halogen Content	BFR/CFR/PVC Free, but Br/Cl >900 ppm in other sources.
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # CAT-038-DCPPS224
D-Sub Crimp: Plug, Signal, 62 Posn,
Pin Size 22, Shell Size 4



TE Part # 1658684-1
HDP-22,RCPT,SIZE 4,62 POSN



TE Part # 5748642-1
KIT,RCPT,62P,HDP-22,SHLD ENCLS



TE Part # 5750727-1
KIT,RCPT,62P,HDP-22,SHLD HDWRE


Customers Also Bought



TE Part #1658651-1
D-Sub Crimp Recpt Signal 37 Posn,
Socket Size 20, Shell Size 4



TE Part #1658652-1
D-Sub Crimp: Plug, Signal, 50 Posn,
Pin Size 20, Shell Size 5



TE Part #1-480510-0
04P .140 MNL PLUG NAT



TE Part #1055692-1
2367 5016 54 OSMT PLUG,2500/RL






TE Part #1-745508-0
FERRULE SPLIT RING, HD



TE Part #1445522-3
MINI CPC



TE Part #YDTS26W25-35SDV001
D38999: Straight Plug, 25-35 Insert



TE Part #1447477-2
J6-2=J6-XX JUMPER, LF



TE Part #1-86264-7
26 MODIV HSG COMP DR .100 EARS



TE Part #1241415-1
AMP MCP 6.3/4.8K, CONTACT, SWS, (LP)

Documents

Product Drawings

KIT,PLUG,62P,HDP-22,SHLD HDWRE

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_5748471-1_O.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_5748471-1_O.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_5748471-1_O.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

AMPLIMITE Subminiature D Connectors - Cable Connectors

English

AMPLIMITE Cable Connectors and Shielding Hardware Kits QRG

English

Product Specifications

Application Specification

English



Instruction Sheets

Instruction Sheet (U.S.)

English

Instruction Sheet (U.S.)

English

Agency Approvals

UL Report

English