



Connectors > D-Shaped Connectors > D-Sub Accessories > D-Sub Backshells & Clamps



D-Shaped Connector Accessories: **Cable Clamp Kit**

Cable Clamp Type: **Two-Piece RFI/EMI Shield**

Compatible With Connector Shell Size: **5**

Shielded: **No**

Cable Insulation Diameter Range: **6.48 – 11.94 mm [.255 – .47 in]**

Features

Product Type Features

Grommets	With
Product Type	Accessory
D-Shaped Connector Accessories	Cable Clamp Kit

Body Features

Shield Plating Material	None
Cable Clamp Material	ABS
Color	Black
Grommets per Set	6
Cable Clamp Type	Two-Piece RFI/EMI Shield
Cable Exit Angle	180° (In-Line)

Mechanical Attachment

Screw & Hole Thread Size	4-40
--------------------------	------

Dimensions

Cable Insulation Diameter Range	6.48 – 11.94 mm[.255 – .47 in]
---------------------------------	--------------------------------



Operation/Application

Compatible With Connector Shell Size	5
Shielded	No

Packaging Features

Packaging Quantity	1
Packaging Method	Kit

Other

Comment	Jackscrews must be purchased separately.
---------	--

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant with Exemptions
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2021 (211) Candidate List Declared Against: JAN 2021 (211) SVHC > Threshold: Pb (.35% in component) Article Safe Usage Statements: Do not eat, drink or smoke when using this product. Wash thoroughly after handling. Recycle if possible and dispose of the article by following all applicable governmental regulations relevant to your geographic location.
Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # 207476-1

CABLE CLAMP KIT,SZ 5

Also in the Series | AMPLIMITE Kit

D-Sub Backshells & Clamps(136)

D-Sub Contact Accessories(1)

D-Sub Covers(3)

D-Sub Locking & Mounting(122)

Customers Also Bought

TE Part #1658640-1

D-Sub Crimp Recpt Signal 50 Posn, Socket Size 20, Shell Size 5

TE Part #1658683-1

D-Sub Crimp Recpt Signal 44 Posn, Socket Size 22, Shell Size 3

TE Part #1-5750913-7

IDC D-Sub: Connector Kit, Plug, Signal, 1.27 mm

TE Part #1658641-1

D-Sub Crimp: Plug, Signal, 50 Posn, Pin Size 20, Shell Size 5

TE Part #1658685-1

HDP-22,RCPT,SIZE 5,78 POSN

TE Part #1617807-4

FC-335-SY4=RELAY, 3PST

TE Part #1658660-1

D-Sub Crimp Recpt Signal 37 Posn, Socket Size 20, Shell Size 4

TE Part #YDTS26W13-35PBV001

D38999: Straight Plug, 13-35 Insert

TE Part #169750-000

S02-09-R



Documents

Product Drawings

2 PC PLST CBL CLMP KIT

English

CAD Files

3D PDF

English

Customer View Model

ENG_CVM_5748678-5_O.2d_dxf.zip

English

Customer View Model

ENG_CVM_5748678-5_O.3d_igs.zip

English

Customer View Model

ENG_CVM_5748678-5_O.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

AMPLIMITE Subminiature D Connectors - Cable Connectors

English

AMPLIMITE Cable Connectors and Shielding Hardware Kits QRG

English

Instruction Sheets

Instruction Sheet (U.S.)

English