



Connectors > D-Shaped Connectors > D-Sub Accessories > D-Sub Backshells & Clamps



D-Shaped Connector Accessories: **Backshell Kit**

Number of Positions: **26**

Shielded: **Yes**

Cable Insulation Diameter Range: **6.86 mm [.27 in]**

Cable Exit Angle: **180° (In-Line)**

Features

Product Type Features

Latching Spring Material	Stainless Steel
Grommets	With
Product Type	Hardware
D-Shaped Connector Accessories	Backshell Kit
Connector & Contact Terminates To	Wire & Cable

Configuration Features

Number of Positions	26
---------------------	----

Body Features

Strain Relief Clip Material	Steel
Backshell Plating Material	Nickel over Copper
Backshell Material	Zinc
Cable Exit Angle	180° (In-Line)

Mechanical Attachment

Screw & Hole Thread Size	2-56 UNC
--------------------------	----------



Dimensions

Cable Insulation Diameter Range	6.86 mm[.27 in]
---------------------------------	-----------------

Operation/Application

Shielded	Yes
----------	-----

Packaging Features

Packaging Quantity	1
Packaging Method	Bag

Other

Comment	Each backshell kit includes upper and lower backshells, two spring latches, one strain relief staple and two 2-56 screws. All are packaged unassembled
---------	--

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2021 (211) Candidate List Declared Against: JAN 2021 (211) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>



Compatible Parts

TE Part # CAT-AM7-2250
IDC D-Sub: Plug Assembly, Signal, 1.27 mm

Also in the Series | AMPLIMITE 0.50 Series

D-Sub Backshells & Clamps(31)

D-Sub Covers(20)

D-Sub Locking & Mounting(8)

IDC D-Sub Connectors(77)

Insertion & Extraction Tools(1)

PCB D-Sub Connectors(196)

Customers Also Bought

TE Part #1-5749111-0
IDC D-Sub: Plug Assembly, Signal, 1.27 mm

TE Part #1658661-1
D-Sub Crimp: Plug, Signal, 50 Posn, Pin Size 20, Shell Size 5

TE Part #17-015A
BOARD LEVEL PRESSURE STOCK LIST

TE Part #1658675-1
D-Sub Crimp: Plug, Signal, 50 Posn, Pin Size 22, Shell Size 1



TE Part #1761028-1
D-Sub Receptacle Assembly: Right Angle, 1.27mm

TE Part #1977890-1
CPC SERIES 6 SEALED TWO-PIECE

TE Part #104072-1
MTE KEYING PLUG

TE Part #1761842-1
CONNECTOR ASSY, 60 DUAL POSITI

TE Part #1757823-8
AMPLIMITE,ASY,PLUG,STD,90,ZN,2,CT

TE Part #8-1622796-7
YR1 0.1% 18K2

Documents

Product Drawings

26 50SR KIT, ST, UK

English

CAD Files

3D PDF

English

Customer View Model

ENG_CVM_749608-2_A.2d_dxf.zip

English

Customer View Model

ENG_CVM_749608-2_A.3d_igs.zip

English

Customer View Model

ENG_CVM_749608-2_A.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

AMPLIMITE Subminiature D Connectors - .050 Series Connector

English

AMPLIMITE .050 Series D-sub Connectors QRG

English

Product Specifications

Application Specification

English



Instruction Sheets

Instruction Sheet (U.S.)

English

Instruction Sheet (U.S.)

English

Instruction Sheet (U.S.)

English

Instruction Sheet (U.S.)

English