



Connectors > D-Shaped Connectors > D-Sub Accessories > D-Sub Contact Accessories



Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2021 (211) Candidate List Declared Against: JAN 2021 (211) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Wave solder capable to 265°C

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # CAT-035-DCRSS203
D-Sub Crimp Recept Signal 25 Posn,
Socket Size 20, Shell Size 3

Customers Also Bought



TE Part #928814-1
FASTON 250 TAB FLAG .032 TPBR LP



TE Part #1735801-1
2.0mm,Crimp,Contact



TE Part #1393122-1
KHAE-17D12-24=KH



TE Part #2176326-1
CRGP 0603 10R 1%



TE Part #2-1462050-2
AXICOM HF RELAY 3GHZ SHIELDED



TE Part #1-770972-0
12P MINI UMNL R/A HDR ASSY LF



TE Part #2-640445-2
22P MTA156 HDR ASSY FL/STR SN



TE Part #104363-1
02 MTE HDR SRST LATCH .100CL



TE Part #1776904-1
CPC POSTED RCPT,17-16,R/A



TE Part #1496476-6
STD USB-A TO MINI-B ASSY, 12"

Documents

Product Drawings

20 DF SOC CONT GOLD FLASH/DUPLEX LP

English

CAD Files

3D PDF

3D



Customer View Model

[ENG_CVM_CVM_7-745288-2_AP.2d_dxf.zip](#)

English

Customer View Model

[ENG_CVM_CVM_7-745288-2_AP.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_7-745288-2_AP.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

[AMPLIMITE Subminiature D Connectors - Cable Connectors](#)

English

[AMPLIMITE Cable Connectors and Shielding Hardware Kits QRG](#)

English