

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2021 (211) Candidate List Declared Against: JAN 2021 (211) Does not contain REACH SVHC
Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

TE Part # 350523-1
15P STR/REL HSG HNGD V0 RED

TE Part # 350374-1
12P STR/REL HSG HNGD V0

TE Part # 350522-1
09P STR/REL HSG HNGD V0 RED




Customers Also Bought




TE Part #1658647-1
D-Sub Crimp: Plug, Signal, 15 Posn,
Pin Size 20, Shell Size 2




TE Part #1658644-1
D-Sub Crimp Recpt Signal 15 Posn,
Socket Size 20, Shell Size 2



TE Part #208491-1
CMC SERIES 2



TE Part #1-640521-0
09P MR II PLUG HSG V0 RED




TE Part #1-640515-0
24P MR II CAP HSG V0 RED



TE Part #205841-2
CPC RECPT ASSEMBLY SIZE 11-8



TE Part #YDTS20F11-35SNV001
D38999: Square Flange, 11-35 insert



TE Part #1-640511-0
09P MR II CAP HSG V0 RED



TE Part #2-350376-0
MR SPLT GROMET .218 DIA BLK LF



TE Part #2-350377-0
MR SPLT GROMET .156 DIA BLK LF

Documents

Product Drawings

MR SPLT GROMET .218 DIA BLK LF

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_2-350378-1_U.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_2-350378-1_U.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_2-350378-1_U.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.



Datasheets & Catalog Pages

SOFT_SHELL_PIN_AND_SOCKET_CONNECTORS_CATALOG

English

Product Specifications

Application Specification

English

Product Environmental Compliance

Product Compliance

English

Product Compliance

English