




Terminals & Splices > Quick Disconnects



Terminal & Splice Type: **Receptacle**
Wire Size: **.32 – .82 mm²**
Quick Disconnect Mating Tab Width: **4.75 mm [.187 in]**
Quick Disconnect Mating Tab Thickness: **.51 mm [.02 in]**

Features

Product Type Features

Wire/Cable Type	Regular Wire
Wire Stop	No
Terminates To	Wire & Cable
Quick Disconnect Insertion Force	Normal
Sealable	No
Insulated	No

Configuration Features

Connection Capacity	Single
---------------------	--------

Electrical Characteristics

Voltage (Max)	600 V
---------------	-------

Body Features

Insulation Material	Nylon
Fully Insulated	No
Quick Disconnect Plating Material	Tin



Contact Features

Terminal Type	Tab
Terminal & Splice Type	Receptacle
Quick Disconnect Terminal Orientation	Straight
Contact Base Material	Brass
Crimp Type	F-Crimp
Barrel Type	Closed

Mechanical Attachment

Mating Retention Type	Dimple
Wire Insulation Support	With

Dimensions

Accepts Wire Insulation Diameter Range	3.43 mm[.135 in]
Overall Length	20.14 mm[.793 in]
Receptacle Terminal Stock Thickness	.41 mm[.016 in]
Wire Size	.32 – .82 mm²
Quick Disconnect Mating Tab Width	4.75 mm[.187 in]
Quick Disconnect Mating Tab Thickness	.51 mm[.02 in]

Usage Conditions

Insulation Requirement	Uninsulated
Operating Temperature Range	-40 – 110 °C[-40 – 230 °F]

Industry Standards

UL Flammability Rating	UL 94V-2
UL Rating	Listed

Packaging Features

Packaging Quantity	1000
Quick Disconnect Packaging Method	Loose Piece/Carton

Other

Barrel Color	Red
--------------	-----

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
------------------------------	-----------




EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2021 (211) Candidate List Declared Against: JAN 2021 (211) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # 58628-2
PROCrimp DIESET 26-14 ULTRAFast



TE Part # 90390-3
DIEs ULTRA-Fast FASTON 22-18 DIE SET



TE Part # 58628-1
PROCrimp T&D 26-14 ULTRAFast



TE Part # 2217481-1
KIT, BTLI, SDE CLOSED HEAD



TE Part # 2217481-2
KIT, BTLI, SDE CLOSED HEAD

Also in the Series | Ultra-Fast 187



Quick Disconnects(47)

Customers Also Bought



TE Part #179861-1
STD Temp Power Double Lock Plug



TE Part #2-2834075-2
SLIMSEAL MINIATURE RECEPTACLES



TE Part #104257-4
05 MTE RCPT HSG SR LATCH .100



TE Part #103653-2
03 MTE SHRD PIN HSG SR LATCH



TE Part #154717-3
PL 250 REC TERMINAL 14-11 AWG TPBR



TE Part #1761686-6
IDC LOW PRO HDR 16P VERT LG LAT



TE Part #2-1658527-5
622-2441LF=FSKT IDC S 24 30AU



TE Part #W2PD
DEUTSCH DT WEDGELOCKS



TE Part #2-2834074-2
SLIMSEAL MINIATURE PLUGS

Documents

Product Drawings

ULTRA-FAST 187 ASY REC 22-18 TPBR

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_2-521103-2_A.2d_dxf.zip



English

Customer View Model

[ENG_CVM_CVM_2-521103-2_A.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_2-521103-2_A.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

[Ultra-Fast and Ultra Fast Plus](#)

English

Product Specifications

[Application Specification](#)

English

Agency Approvals

[Agency Approval Document](#)

English