8-2823056-8 SUPERSEDED

Micro-MaTch Value Line


TE Internal #: 8-2823056-8

TE Internal Description: 18P,FOB,SMD W/ LATCH,P&P, MM VALUE LINE

FEMALE-ON-BOARD CON TOP ENTRY VALUE-LINE

View on TE.com >







All FEMALE-ON-BOARD CON TOP ENTRY VALUE-LINE (1)

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2021 (211) Candidate List Declared Against: JUL 2017 (174) SVHC > Threshold: Not Yet Reviewed
Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Reflow solder capable to 260°C

Product Compliance Disclaimer


This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: https://echa.europa.eu/guidance-documents/guidance-on-reach

Also in the Series | Micro-MaTch Value Line



Ribbon Cable Connectors(3)


Customers Also Bought




TE Part #205714-7
D-Sub Plug Assembly: Vertical, Shell Size 4, 2.74mm



TE Part #1437652-1
6PCR-08-008=6 SERIES ASSEMBLY




TE Part #2-2176371-6
RQ 0603 8K45 0.1% 10PPM 5K RL




TE Part #1445729-1
MTG BRKT,OVAL HOLE



TE Part #8-338728-6
MALE-ON-BOARD CONNECTOR



TE Part #3-647166-7
Nylon Vertical PCB Header: 2.54mm, Surface Mount, MTA 100



TE Part #3-2176155-2
Metal Chip Resistor: Current Sense



TE Part #2-2303816-4
DEUTSCH DT Series Housings & Connectors



TE Part #109452-4
RING TONGUE 170 18-14 AWG PTPBR



TE Part #4-103795-0
80 MODII HDR DRRA B/A .100CL

Documents

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_8-2823056-8_A.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_8-2823056-8_A.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_8-2823056-8_A.3d_stp.zip

English

By downloading the CAD file I accept and agree to the Terms and Conditions of use.

Datasheets & Catalog Pages

1-1773840-5_MICRO-MATCH-VALUE-LINE-QRG

English

Product Specifications

Application Specification

English

Product Environmental Compliance

Product Compliance

English

Product Compliance

English