



Terminals & Splices > Terminal Housings, Insulation Sleeves & Blocks > Crimp Terminal Housings



Terminal & Splice Type: **Receptacle**
Housing Type: **Receptacle**
Number of Crimp Terminal Housing Positions: **4**
Crimp Terminal Housing Terminal Orientation: **Straight**
Crimp Terminal Housing Housing Color: **Black**

Features

Product Type Features

Product Type	Terminal Housing
Terminates To	Wire & Cable
Housing Type	Receptacle
Sealable	No
Insulated	No

Configuration Features

Number of Crimp Terminal Housing Positions	4
--	---

Body Features

Crimp Terminal Housing Housing Color	Black
Crimp Terminal Housing Mating Retention	With
Crimp Terminal Housing Mating Alignment	With

Contact Features

Terminal & Splice Type	Receptacle
Crimp Terminal Housing Terminal Orientation	Straight



Mechanical Attachment

Mating Retention Type	Latch
Crimp Terminal Housing Mounting Style	Cable Mount (Free-Hanging)

Housing Features

Crimp Terminal Housing Housing Material	Polyamide
---	-----------

Dimensions

Length	18 mm[.708 in]
Crimp Terminal Housing Centerline	5 mm[.196 in]

Usage Conditions

Operating Temperature Range	-40 – 105 °C[-40 – 221 °F]
-----------------------------	----------------------------

Packaging Features

Packaging Quantity	10000
Crimp Terminal Housing Packaging Method	Carton

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2021 (211) Candidate List Declared Against: JAN 2021 (211) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not reviewed for solder process capability










Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides



on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

 TE Part # 1-480281-0 FF 250 REC HSG 6P NYLON BLACK	 TE Part # 180907-5 FF 250 REC HSG 2P NYLON BLACK	 TE Part # 925015-1 FF 110 REC HSG 3P NYLON BLACK	 TE Part # 626056 FASTIN-ON 110 HOUSING REC PA66 NATURAL
 TE Part # 172133-2 FF 250 REC HSG 4P NYLON BLACK	 TE Part # 172134-2 FF 250 PLUG HSG 4P NYLON BLACK	 TE Part # 926728-1 FF 110 REC HSG 4P NYLON BLACK	 TE Part # 180923-5 FF 250 REC HSG 2P NYLON BLACK
 TE Part # 180941-5 FF 250 REC HSG 3P NYLON BLACK	 TE Part # 626056-5 FASTIN-ON .110 HOUSING RECEPTACLE RED	 TE Part # 925015-3 FF 110 REC HSG 3P NYLON NAT	 TE Part # 626057-1 FASTIN-ON .110 HOUSING TAB NYLON 6/6
 TE Part # 1534690-1 FASTIN FASTON HOUSING 4POS 2,8 MM	 TE Part # 626064-5 ISOLADOR	 TE Part # 881507-9 FASTIN-ON 2.8,TERMINAL,FAM SLD /UNSLD,CB	

Also in the Series | FASTIN-FASTON 110



Automotive Housings(1)



Automotive Terminals(4)



Crimp Terminal Housings(35)



Insertion & Extraction Tools(3)




Quick Disconnects(84)


Customers Also Bought



TE Part #303696-000
Heat Shrink Boots: Non Lipped, Right Angle



TE Part #626056-5
FASTIN-ON .110 HOUSING RECEPTACLE RED



TE Part #3822713001
44A1131-20-0/1/9-9



TE Part #9531963001
100G1131-1.20-2/6/9-0



TE Part #2819013001
44/7031-16-1



TE Part #5428003001
44/7031-16-45




TE Part #2813593001
44/7031-16-6



TE Part #5161500-8
minimatch 8 pos male



TE Part #5161500-9
minimatch 9 pos male



TE Part #3189214001
DCPT-3/1-45-SP

Documents



Product Drawings

FASTIN-ON .110 HOUSING REC PRETO/BLACK

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_626056-4_J_c-626056-4-j.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_626056-4_J_c-626056-4-j.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_626056-4_J_c-626056-4-j.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

White Paper: Nylon Discoloration

English

Product Specifications

Application Specification

English