



Terminals & Splices > Terminal Housings, Insulation Sleeves & Blocks > Crimp Terminal Housings



Terminal & Splice Type: **Tab**
Housing Type: **Tab Housing**
Number of Crimp Terminal Housing Positions: **2**
Crimp Terminal Housing Terminal Orientation: **Straight**
Crimp Terminal Housing Housing Color: **Black**

Features

Product Type Features

Product Type	Terminal Housing
Terminates To	Wire & Cable
Connector System	Wire-to-Wire
Housing Type	Tab Housing
Sealable	No
Insulated	No

Configuration Features

Number of Crimp Terminal Housing Positions	2
--	---

Body Features

Crimp Terminal Housing Housing Color	Black
Crimp Terminal Housing Mating Retention	With
Crimp Terminal Housing Mating Alignment	With

Contact Features

Terminal & Splice Type	Tab
------------------------	-----



Crimp Terminal Housing Terminal Orientation	Straight
---	----------

Mechanical Attachment

Mating Retention Type	Latch
Crimp Terminal Housing Mounting Style	Cable Mount (Free-Hanging)

Housing Features

Crimp Terminal Housing Housing Material	Polyester
---	-----------

Dimensions

Length	13.3 mm[.524 in]
Width	26 mm[1.023 in]
Crimp Terminal Housing Centerline	5 mm[.196 in]

Usage Conditions

Operating Temperature Range	-30 – 105 °C[-22 – 221 °F]
-----------------------------	----------------------------

Packaging Features

Packaging Quantity	800
Crimp Terminal Housing Packaging Method	Carton

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2021 (211) Candidate List Declared Against: JAN 2021 (211) Does not contain REACH SVHC
Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Not applicable for solder process capability









Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part





numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

 TE Part # 180924 FF 250 TAB HSG 2P NYLON NAT	 TE Part # 180908-5 FF 250 TAB HSG 2P NYLON BLACK	 TE Part # 480053-4 FF 250 TAB HSG 1P NYLON BLACK	 TE Part # 180906-5 FF 250 TAB HSG 6P NYLON BLACK
 TE Part # 928193-1 FF 2.8MM TAB HSG 2P PBT BLACK	 TE Part # 626065-5 HOUSING 2P .110 FASTIN-ON TAB	 TE Part # 4-180924-0 FF 250 TAB HSG 2P NYLON NAT	 TE Part # 1-480282-0 FF 250 TAB HSG 6P NYLON BLACK
 TE Part # 1-880298-0 FASTON .250 SERIES (6.3 MM) HOUSING	 TE Part # 175978-1 CAP HOUSING 187 (4.8 MM) ASSEMBLY	 TE Part # 880310-9 2 WAY FF 250 HOUSING TAB PA 6.6 BLACK	


Also in the Series | FASTIN-FASTON 110

 Automotive Housings(1)	 Automotive Terminals(4)	 Crimp Terminal Housings(35)	 Insertion & Extraction Tools(3)
---	--	--	--



Quick Disconnects(84)

Customers Also Bought




TE Part #180916-5
FF 250 TAB HSG 1P NYLON BLACK




TE Part #1-967623-5
TIMER, CONNECTOR HOUSING



TE Part #1418985-2
TIMER ACCESSORIES



TE Part #967635-1
2.0 KONT



TE Part #1-929505-4
TAB HSG .110 (2.8 MM) HSG TAB

Documents

Product Drawings

FF 2P HOUSING TAB POLYESTER VALOX 357

English

CAD Files

3D PDF

English

Customer View Model

ENG_CVM_964586-1_A.2d_dxf.zip

English

Customer View Model

ENG_CVM_964586-1_A.3d_igs.zip

English

Customer View Model

ENG_CVM_964586-1_A.3d_stp.zip

English

By downloading the CAD file I accept and agree to the Terms and Conditions of use.



Datasheets & Catalog Pages

White Paper: Nylon Discoloration

English

Product Specifications

Application Specification

English