

TXR40AU90-1007BI

✓ ACTIVE

Raychem | Raychem TXR

TE Internal #: C42433-000

Raychem TXR, Ruggedized Backshells & Adapters

[View on TE.com >](#)



Connectors > Connector Backshells & Adapters > Ruggedized Backshells & Adapters



Connector General Specification Number: MIL-DTL-38999 Series III/Class C,F,K,W, MIL-DTL-38999 Series IV/Class C,F,W, MIL-DTL-38999 Series IV/Class C,W, MIL-DTL-38999 Series IV/Class F,W

Backshell Material: Aluminum

Adapter Plating Material: Zinc Cobalt

Cable Diameter Range: 5.6 – 8.9 mm [.219 – .35 in]

Adapter Angle: 90

Features

Product Type Features

Termination Device Included	TR07BI
Pluggable I/O Accessory Type	Tinel-Lock Adapter
Adapter Angle	90
Termination Device Type	Side-Entry Tinel-Lock Ring, Tinel-Lock Adapter, Tinel-Lock Ring
Connector Shell Size	11, B

Body Features

Adapter Underplating Material	Electroless Nickel
Color	Olive Drab
Backshell Material	Aluminum
Adapter Plating Material	Zinc Cobalt
TE Adapter Code	40
Adapter Entry Size	7

Termination Features

Overbraid Termination	Tinel-Lock Ring
-----------------------	-----------------

Dimensions

Cable Entry Diameter	.2 – 11.1 mm[.01 – .44 in]
Cable Diameter Range	5.6 – 8.9 mm[.219 – .35 in]



Usage Conditions

Salt Spray Resistance	48 Hr
Operating Temperature Range	-65 – 175 °C[-85 – 347 °F]

Industry Standards

Connector Detail Specification Number	D38999/20, D38999/24, D38999/26, D38999/40, D38999/42, D38999/46, D38999/47
---------------------------------------	---

Other

Connector General Specification Number	MIL-DTL-38999 Series III/Class C,F,K,W, MIL-DTL-38999 Series IV/Class C,F,W, MIL-DTL-38999 Series IV/Class C,W, MIL-DTL-38999 Series IV/Class F,W
--	---

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant with Exemptions
EU ELV Directive 2000/53/EC	Not Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2021 (211) Candidate List Declared Against: JAN 2021 (211) SVHC > Threshold: Pb (.3% in BODY & NUT) Article Safe Usage Statements: Do not eat, drink or smoke when using this product. Wash thoroughly after handling. Recycle if possible and dispose of the article by following all applicable governmental regulations relevant to your geographic location.
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>



Compatible Parts

TE Part # 173643-000
RH-3960-1-TINEL-KIT-120V

Also in the Series | Raychem TXR

Ruggedized Backshells & Adapters
(2821)

Screened Backshells & Adapters(1)

Customers Also Bought

TE Part #811554-000
Low Profile HS Boots: Blow Molded,
Slim Line, Lipped, Straight

TE Part #825083-000
322A123-4/42-0

TE Part #462378-000
Low Profile Heat Shrink Boots: Poly
Mold, Lipped, Right Angle


TE Part #YDTS26F15-15SBV001
D38999: Straight Plug, 15-15 Insert

TE Part #5580634002
Single Wall VPB: Heat Shrink Tubing, 2:
1 Shrink Ratio


TE Part #265601-000
81044/9-8-3

TE Part #819099-000
381A304-51-0

TE Part #395605-000
44A0141-20-MST4CS2275



TE Part #620067N004
D-108-09CS948



TE Part #CB2963-000
TXR54SJ00-2812BI

Documents

Product Drawings

TXR40AU90-1007BI

English

Datasheets & Catalog Pages

Circular Backshells

English