



Connectors > Rectangular Connectors > Standard Rectangular Connectors



Connector Product Type: **Housing Kit**
Connector & Housing Type: **Plug**
Mating Alignment: **With**
Mating Alignment Type: **Keyed**
Mating Retention: **With**

Features

Product Type Features

Shell Size	25.4 [1.0]
Boxmount	No
Connector Type	Connector Assembly Kit
Kit Type	Connector Kit
Housing Type	EME Mount
Connector Product Type	Housing Kit
Connector & Housing Type	Plug
Connector System	Wire-to-Wire
Sealable	Yes
Connector & Contact Terminates To	Wire & Cable

Configuration Features

Keying	AC
PCB Mount Orientation	Vertical
Number of Positions	20
Number of Rows	2
Panel Gasket	Without

Electrical Characteristics

Operating Voltage	954 VDC
-------------------	---------



Body Features

Plating Material	Nickel
------------------	--------

Contact Features

Contact Type	Socket
Wire Contact Termination Area Plating Material	Gold
Contact Mating Area Plating Material	Gold
Contact Retention Within Housing	With
Contact Current Rating (Max)	5 A

Termination Features

Termination Method to Wire & Cable	Crimp
------------------------------------	-------

Mechanical Attachment

Mating Hardware	Quick Disconnect
Flange	Without
Contact Retention Type Within Housing	Retention Clip
Mating Alignment	With
Mating Alignment Type	Keyed
Mating Retention	With
Mating Retention Type	Jackscrew
Connector Mounting Type	Fixing Screw

Housing Features

	1 in
--	------

Dimensions

Row-to-Row Spacing	2.54 mm[.1 in]
--------------------	----------------

Usage Conditions

Operating Temperature Range	-65 – 125 °C[-85 – 257 °F]
-----------------------------	----------------------------

Operation/Application

Shielded	No
Circuit Application	Power & Signal

Industry Standards

UL Flammability Rating	UL 94V-0
------------------------	----------

Product Compliance



For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2021 (211) Candidate List Declared Against: JAN 2021 (211) Does not contain REACH SVHC
Halogen Content	Not Yet Reviewed for halogen content
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

TE Part # A41825-000
[MTCPQKT1R2PFAC](#)

Customers Also Bought

TE Part #EF9981-000
[Bulbous Heat Shrink Boots: Lipped, Right Angle](#)

TE Part #1757624-1
[SZ 8 COAX PIN, RG142, HEX CRIMP](#)

TE Part #204502-4
[RECEPT ASSY, 26 POSN, AMPLIMITE](#)

TE Part #205162-6
[AMPLIMITE, ASY, PLUG, 109, 1](#)

MTCPQKT1P2SFAC

Standard Rectangular Connectors, Housing Kit, Plug, Mating Alignment, Keyed Mating Alignment Type, Mating Retention, Jackscrew Mating Retention Type





TE Part #YACT26MA98SEV00100
Straight Plug D38999, A98 Insert



TE Part #YACT26MG35SCV00100
Straight Plug D38999, G35 Insert

TE Part #2102579-1
ASSY 2 AL COPALUM LITE DUAL HOLE 3/8



TE Part #YACT24MA98SNV00100
JAM NUT RECEPTACLE



TE Part #F78598-000
B-155-1504



TE Part #ZPF000000000163975
DMC-M 99-04 CN (=33537-PC000)

Documents

Product Drawings

MTCPQKT1P2SFAC

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_E18575-000_R.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_E18575-000_R.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_E18575-000_R.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

Products for Aerospace and Defense

English

Product Specifications

MTC Quick-Disconnect Connectors with Removable Contacts

English