



Connectors > Rectangular Connectors > Rectangular Contact Inserts



Sealable: No

Features

Product Type Features

Product Type	Contact
Sealable	No

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Not Yet Reviewed
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2021 (211) Candidate List Declared Against: JAN 2020 (205) SVHC > Threshold: Not Yet Reviewed
Halogen Content	Not Yet Reviewed for halogen content
Solder Process Capability	Not reviewed for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products



will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

TE Part # T2090002101-001
PNEU-C-M1.6

Also in the Series

HDC HMN

Connector Contacts(2)

Insertion & Extraction Tools(1)

Rectangular Connector Hardware(16)

Rectangular Contact Inserts(111)

Customers Also Bought

TE Part #YACT26JE35HNV00100
Straight Plug D38999, E35 Insert

TE Part #YDTS26F17-35SNC001
Straight Plug: D38999, 17-35 Insert, Electroless Nickel Plating

TE Part #ZPF000000000003686
732-8020-04

TE Part #ZPF000000000113361
DMC-MD 80 AJ 01

TE Part #225398-6
CONNECTOR, BNC DUAL CRIMP JACK

TE Part #ZPF000000000003693
732-8021-04 B

TE Part #ZPF000000000201129
732-8052-31 WA

TE Part #ZPF0000000000015141
DMC-M 01-08 AB



TE Part #ZPF00000000203708
DMC-M 99-10 PC



TE Part #CZ6862-000
HEX40-AC-45-25-A12-3

Documents

Product Drawings

PNEU-C-F1.6

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_T2090002201-001_A.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_T2090002201-001_A.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_T2090002201-001_A.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

HEAVY DUTY CONNECTORS

English