



Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2021 (211) Candidate List Declared Against: JAN 2020 (205) SVHC > Threshold: Not Yet Reviewed
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>



Also in the Series

Universal MATE-N-LOK

Circular Power Connectors(2)	Connector Contacts(11)	Insertion & Extraction Tools(4)	Power Contacts(207)
Rectangular Boots & Strain Relief(35)	Rectangular Connector Adapters(7)	Rectangular Connector Housings(2)	Rectangular Connector Keying Plugs(3)
Rectangular Connector Locking(4)	Rectangular Connector Seals(26)	Rectangular Power Connectors(725)	

Customers Also Bought

TE Part #1735482-2 Free Height Receptacle Conn: Board-Board, Vertical, 60, 0.8mm	TE Part #3-1630027-2 Power Resistors: Aluminum Housed, HSC	TE Part #926895-7 UNIVERSAL M-N-L SOCKET	TE Part #1614770-4 Resistor Power BDS2A250
TE Part #284874-1 24 POS PLUG HOUSING ASS'Y	TE Part #4-1393243-2 RT423024	TE Part #55992-1 AMPOWER TERMINAL 2 STUD HOLES	TE Part #1241390-2 AMP MCP, RECEPTACLE AND TAB



Documents

Product Drawings

02P UMNL CAP HSG, HI TEMP, SPECIAL PKG

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_8-794815-1_B_c-8-794815-1-b.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_8-794815-1_B_c-8-794815-1-b.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_8-794815-1_B_c-8-794815-1-b.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

SOFT_SHELL_PIN_SOCKET_CONNECTORS_STANDARD_DENSITY

English

Product Specifications

Application Specification

English

Agency Approvals

UL Report

English