



Connectors > PCB Connectors > Wire-to-Board Connectors > FFC, FPC & Ribbon Connectors > FFC Connectors > 2.54mm FFC Connectors Receptacle Housing



FFC Connector Product Type: **Housing**

Connector System: **Wire-to-Board**

Number of Positions: **10**

Centerline (Pitch): **2.54 mm [.1 in]**

Number of Rows: **1**

[All 2.54mm FFC Connectors Receptacle Housing \(143\)](#)

Features

Product Type Features

Connector & Housing Type	Receptacle
FFC Connector Product Type	Housing
Connector System	Wire-to-Board
Sealable	No
Connector & Contact Terminates To	Wire & Cable
Insertion Force Type	Normal

Configuration Features

Compatible With Wire & Cable Type	FFC
Number of Positions	10
Number of Rows	1

Electrical Characteristics

Dielectric Withstanding Voltage (Max)	720 VAC
---------------------------------------	---------



Insulation Resistance	5000 MΩ
Operating Voltage	300 VAC

Contact Features

Contact Type	Socket
--------------	--------

Mechanical Attachment

Mating Alignment Type	Polarization
Mating Retention Type	Detent
Mating Retention	With
Mating Alignment	With
Panel Mount Feature	Without
Connector Mounting Type	Cable Mount (Free-Hanging)

Housing Features

Housing Material	PBT GF
Centerline (Pitch)	2.54 mm[.1 in]
FFC Cable Entry	Straight
Housing Color	Black

Usage Conditions

Operating Temperature Range	-65 – 105 °C[-85 – 221 °F]
-----------------------------	----------------------------

Operation/Application

Circuit Application	Signal
---------------------	--------

Industry Standards

UL Flammability Rating	UL 94V-0
------------------------	----------

Packaging Features

Packaging Quantity	1
Packaging Method	Package

Other

Comment	Use Extraction Tool No. 91092-1 for round wire contacts.
---------	--

Product Compliance

For compliance documentation, visit the product page on [TE.com](#)>

EU RoHS Directive 2011/65/EU	Compliant
------------------------------	-----------







EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2021 (211) Candidate List Declared Against: JAN 2021 (211) Does not contain REACH SVHC
Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>


Compatible Parts

 TE Part # CAT-F439-S01339254 2.54mm FFC Connectors Socket Contacts	 TE Part # CAT-F439-S01339127 1.27mm FFC Connectors Socket Contacts	 TE Part # CAT-F439-P65127 1.27mm FFC Connectors Pin Contacts	 TE Part # CAT-F439-P65254 2.54mm FFC Connectors Pin Contacts
 TE Part # 485893-8 010 HOUSING FFC PIN 100CL SR	 TE Part # 1761852-1 FFC RCPT HP 100SNPB RL NO LUBE	 TE Part # 1-487137-1 FFC SOLDER TAB FULL 100 SN	 TE Part # 487787-3 FFC SPLICE CONTACT L.P.





TE Part # 487843-1
FFC SPLICE CONTACT




TE Part # 494060-3
FFC TERMINAL PLT

Customers Also Bought



TE Part #1-487545-4
FFC Receptacle Housing: 1.27mm



TE Part #1-5499345-1
AMP-LATCH UNIVERSAL HEADERS



TE Part #1-534267-0
18 MODIV VRT DR OE 100/125



TE Part #CB2042-000
B-155-9101



TE Part #1-86557-4
2.54mm FFC Connectors Pin Contacts



TE Part #1-172160-9
MINI UNIVERSAL M-N-L CAP 6P




TE Part #1-172162-2
12 POS TR MINI UNIV



TE Part #1-172168-9
MINI UNIVERSAL M-N-L PLUG 6P



TE Part #1-172170-2
12 POS TR MINI UNIV



TE Part #1-172233-9
2P MINI UNIV FREE HANG BLACK

Documents

Product Drawings

010 HOUSING FFC RCPT SR 100CL

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_88859-3_AL.2d_dxf.zip



English

Customer View Model

[ENG_CVM_CVM_88859-3_AL.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_88859-3_AL.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Specifications

[Application Specification](#)

English

Product Environmental Compliance

[TE Material Declaration](#)

English

Instruction Sheets

[Instruction Sheet \(U.S.\)](#)

English

[Extraction Tools](#)

English

Agency Approvals

[CSA Certificate](#)

English