




Connectors > PCB Connectors > Wire-to-Board Connectors > Wire-to-Board Connector Assemblies & Housings



Connector Product Type: **Housing**

Connector & Housing Type: **Receptacle**

Connector System: **Wire-to-Board**

Number of Positions: **2**

Centerline (Pitch): **5 mm [.197 in]**

Features

Product Type Features

Connector Product Type	Housing
Connector & Housing Type	Receptacle
Connector System	Wire-to-Board
Sealable	No
Connector & Contact Terminates To	Wire & Cable

Configuration Features

Keying & Polarized Rib Location	1b/2b
Number of Positions	2
Number of Rows	1

Termination Features

Termination Method to Wire & Cable	Crimp
------------------------------------	-------

Mechanical Attachment

Locking Latch Between Cavity Number	1&2
Strain Relief	Without



Panel Mount Feature	Without
PCB Mount Retention	Without
Mating Retention Type	Latch
Mating Retention	With
Connector Mounting Type	Cable Mount (Free-Hanging)

Housing Features

Housing Material	PA 6.6
Centerline (Pitch)	5 mm[.197 in]
Housing Color	Violet

Dimensions

Connector Length	10 mm[.39 in]
Connector Height	12.2 mm[.48 in]

Usage Conditions

Operating Temperature Range	-40 – 105 °C[-40 – 221 °F]
-----------------------------	----------------------------

Operation/Application

Circuit Application	Power
---------------------	-------

Industry Standards

RAST Version	02-B
Glow Wire Rating	Standard Part - Not Glow Wire
UL Flammability Rating	UL 94V-2

Packaging Features

Packaging Quantity	2500
Packaging Method	Bag

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2021 (211) Candidate List Declared Against: JAN 2021 (211)



Does not contain REACH SVHC

Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
-----------------	---

Solder Process Capability	Not applicable for solder process capability
---------------------------	--

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

 TE Part # 928343-2 STD-TIM GEH 2P	 TE Part # 928344-2 STD-TIMER GEH 2P	 TE Part # 928344-7 7P STD-TIMER GEH	 TE Part # 928344-4 4P STD TIMER GEH
 TE Part # 928344-3 3P STD TIMER GEH	 TE Part # 3-928344-4 4P STD TIMER GEH	 TE Part # 5-928344-4 STD TIMER HOUSING 4POS	 TE Part # 1-928344-2 STD-TIMER GEH 2P
 TE Part # 1241981-3 STD TIMER HOUSING 3P (NATURE)	 TE Part # 6-928344-2 STD-TIMER GEH 2P	 TE Part # 7-928344-2 STD-TIMER GEH 2P	



Also in the Series | RAST 5 IDC Connectors

Automotive Terminals(8)	Connector Contacts(12)	Crimp Terminal Housings(41)	Insertion & Extraction Tools(1)
Rectangular Connector Housings(1)	Standard Edge Connectors(36)	Standard Rectangular Connectors(138)	Wire-to-Board Connector Assemblies & Housings(214)
Wire-to-Board Connector Contacts(2)	Wire-to-Board Headers & Receptacles (424)		

Customers Also Bought

TE Part #2176407-8 3560 27K 1%	TE Part #4-2176327-8 CRGP 0805 82K 1%	TE Part #1776003-2 CONTACT ASSY,SCKT,.045 POST LP	TE Part #1934351-1 TinMan R/A header Assy 4x16 open
TE Part #5177985-9 Free Height Receptacle Conn: Board-Board, Vertical, 180, 0.8mm	TE Part #160759-3 250 PL MKI REC. 20-15AWG TPBR	TE Part #42475-3 FASTON 250 TERMINAL TAB 22-18 AWG BR	TE Part #1888972-3 Cage Assy PCI Hsink LP QSFP Thru Bezel



Documents

Product Drawings

STD-TIMER GEH 2P

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_8-928344-2_B.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_8-928344-2_B.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_8-928344-2_B.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Agency Approvals

VDE Certificate

English

VDE Certificate

English