



Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2021 (211) Candidate List Declared Against: JAN 2020 (205) SVHC > Threshold: Not Yet Reviewed
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



Customers Also Bought



<p>TE Part #1622308-1 LR1 1% 120R</p>	<p>TE Part #1-770988-0 MINI UMNL SOK 22-18AWG AU</p>	<p>TE Part #180901 FF 250 TAB HSG 4P NYLON NAT</p>	<p>TE Part #32151 SPLICE,SOLIS BUTT 12-10</p>
<p>TE Part #215460-4 MICRO-MATCH FEM.SE</p>	<p>TE Part #180907 FF 250 REC HSG 2P NYLON NAT</p>	<p>TE Part #2834089-3 5.0MM SIDE ENTRY MSC 4P_GY</p>	<p>TE Part #280358 AMPMODU II REC. HSG, SINGLE ROW 2 POS</p>
<p>TE Part #1721929-1 PCFN SOLAR RELAY</p>	<p>TE Part #926980-2 CI 2 STIFT</p>		

Documents

Product Drawings

CI 2 STIFT

English

CAD Files

3D PDF

English

Customer View Model

ENG_CVM_926983-2_O.3d_igs.zip

English

Customer View Model

ENG_CVM_926983-2_O.3d_stp.zip

English

Customer View Model

ENG_CVM_926983-2_O.2d_dxf.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.