



RAST | [RAST 5 IDC Connectors](#), [RAST 5D](#)

TE Internal #: 927156-1

RAST 5 IDC Connectors, Housing, Receptacle, Wire-to-Board, 3 Position, 5mm [.197in] Centerline, Insulation Displacement Crimp (IDC), 1 Row

[View on TE.com >](#)

Connectors > PCB Connectors > Wire-to-Board Connectors > Wire-to-Board Connector Assemblies & Housings



Connector Product Type: **Housing**

Connector & Housing Type: **Receptacle**

Connector System: **Wire-to-Board**

Number of Positions: **3**

Centerline (Pitch): **5 mm [.197 in]**

Features

Product Type Features

Connector Product Type	Housing
Connector & Housing Type	Receptacle
Connector System	Wire-to-Board
Sealable	No
Connector & Contact Terminates To	Wire & Cable

Configuration Features

Number of Positions	3
Number of Rows	1

Termination Features

Termination Method to Wire & Cable	Insulation Displacement Crimp (IDC)
------------------------------------	-------------------------------------

Mechanical Attachment

Mating Retention Type	Lock
Mating Retention	With
Connector Mounting Type	Cable Mount (Free-Hanging)



Housing Features

Housing Material	Nylon
Centerline (Pitch)	5 mm[.197 in]
Housing Color	Natural

Usage Conditions

Operating Temperature Range	-25 – 105 °C[-13 – 221 °F]
-----------------------------	----------------------------

Operation/Application

Circuit Application	Power
---------------------	-------

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2021 (211) Candidate List Declared Against: JAN 2021 (211) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability


Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # 1703129-1
8POS MT - EDGE HOUSING



TE Part # 1703081-1
3POS MT - EDGE HOUSING



TE Part # 1703119-1
7POS MT - EDGE HOUSING



TE Part # 927157-1
4P MT-EDGE GEH



TE Part # 928017-1
6P MT-EDGE GEH



TE Part # 927155-1
2P MT-EDGE GEH



TE Part # 1703128-1
8POS MT - EDGE HOUSING



TE Part # 1703071-1
2POS MT-EDGE HOUSING



TE Part # 1703111-1
6POS MT - EDGE HOUSING



TE Part # 1703114-1
6POS MT - EDGE HOUSING

Also in the Series | **RAST 5 IDC Connectors**



Automotive Terminals(8)



Connector Contacts(12)



Crimp Terminal Housings(41)



Insertion & Extraction Tools(1)



Rectangular Connector Housings(1)



Standard Edge Connectors(36)




Standard Rectangular Connectors(138)



Wire-to-Board Connector Assemblies & Housings(214)



Wire-to-Board Connector Contacts(2)



Wire-to-Board Headers & Receptacles (424)

Also in the Series | RAST 5D



Automotive Terminals(4)




Connector Contacts(10)



Insertion & Extraction Tools(1)



Wire-to-Board Connector Assemblies & Housings(92)



Wire-to-Board Headers & Receptacles (84)

Customers Also Bought



TE Part #1658528-4
636-2041LF FEM SOCKET, LEAD FREE



TE Part #2-1376391-3
STD Temp Power Key Plug



TE Part #927155-1
2P MT-EDGE GEH



TE Part #150571-2
FF 110 REC 0.2-0.56MM2 TPBR



TE Part #1-284932-1
DUOPLUG STD 11 POS POL FULLY LOADED 9/10



TE Part #160870-1
FF 250 REC 0.5-1.0MM2 BR



TE Part #1703114-1
6POS MT - EDGE HOUSING



TE Part #2150473-1
OC-AT-E-FM-130F180F-001-0256



Documents

Product Drawings

[3P MT-EDGE GEH](#)

English

CAD Files

Customer View Model

[ENG_CVM_927156-1_A.3d_stp.zip](#)

English

Customer View Model

[ENG_CVM_927156-1_A.2d_dxf.zip](#)

English

[3D PDF](#)

English

Customer View Model

[ENG_CVM_927156-1_A.3d_igs.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Environmental Compliance

[Product Compliance](#)

English

[Product Compliance](#)

English