



Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2021 (211) Candidate List Declared Against: JAN 2021 (211) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # 6-1579007-1
EXTRACTION TOOL



TE Part # 1452426-1
EXTRACTION TOOL




TE Part # 539682-2
ERGOCRIMP DIE SET MQS

Also in the Series | MQS



Automotive Connector Caps & Covers
(133)



Automotive Connector EMC Shielding
(2)



Automotive Connector Locks &
Position Assurance(29)



Automotive Headers(207)




Automotive Housings(498)



Automotive Seals & Cavity Plugs(26)



Automotive Terminals(98)



Data Connectivity Headers(1)




Insertion & Extraction Tools(42)



Other Automotive Connector
Accessories(13)

Customers Also Bought



TE Part #2106091-3
4 pos Inverted Thru Board SMT Header



TE Part #173707-1
Econoseal Receptacles and Tabs



TE Part #1565894-1
TH/.025 CONNECTOR SYSTEM,
HOUSING



TE Part #1-967584-1
MQS, CONNECTOR HOUSING



TE Part #1-968876-1
AMP MCP 2.8, CONTACT SWS (LP)

TE Part #1-968875-1
AMP MCP 2.8, CONTACT SWS (LP)

TE Part #1-963745-2
SPECIAL TERMINAL 20-17 AWG SLIPB LP

TE Part #ZPF000000000112972
CONTACT FEMALE 1,6 - 0,35 TO 1,82 MM S/A

Documents

CAD Files

Customer View Model

ENG_CVM_1-963725-1_C9.3d_igs.zip

English

Customer View Model

ENG_CVM_1-963725-1_C9.3d_stp.zip

English

Customer View Model

ENG_CVM_1-963725-1_C9.2d_dxf.zip

English

3D PDF

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Specifications

Application Specification

English