

# W57-XB1A4A10-5 ✓ ACTIVE

## Potter & Brumfield W57

TE Internal #: 1-1423364-2

Potter & Brumfield W57, Circuit Breakers, Thermal, Series Trip, White with Red Rate Marking (Vertical) Button Color, 250VAC Voltage Rating AC

[View on TE.com >](#)



Relays, Contactors & Switches > Circuit Breakers



Circuit Breaker Type: **Thermal**

Circuit Function: **Series Trip**

Illuminated: **No**

Button Color: **White with Red Rate Marking (Vertical)**

Voltage Rating AC: **250 VAC**

### Features

#### Product Type Features

Illumination Type	No Light
Product Type	Circuit Breaker
Actuator Type	Push to Reset
Circuit Breaker Type	Thermal
Illuminated	No

#### Configuration Features

	.441 x .394 in
Earthing Switch	Without
Circuit Function	Series Trip

#### Electrical Characteristics

Voltage Rating AC	250 VAC
Voltage Rating DC	50 VDC
Circuit Breaker Current Rating	5 A
Interrupt Capacity	1000A @ 250VAC/50VDC

#### Body Features

Button Color	White with Red Rate Marking (Vertical)
--------------	--

#### Contact Features

Pole Configuration	1
--------------------	---



Trip Time at 200% 4 – 40 seconds

### Termination Features

Circuit Breaker Termination Type 6.35 [.25] Straight Quick Connect Tab

### Mechanical Attachment

Mounting Hardware Packaging Assembled to Bushing

Mounting Options Knurled Nut/Hex Nut

Mounting Bushing 9.8 x 9.6mm Long, Plastic

Circuit Breaker Mounting Type Panel Mount

### Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU Compliant with Exemptions

EU ELV Directive 2000/53/EC Not Compliant

China RoHS 2 Directive MIIT Order No 32, 2016 Restricted Materials Above Threshold

EU REACH Regulation (EC) No. 1907/2006  
 Current ECHA Candidate List: JAN 2021 (211)  
 Candidate List Declared Against: JAN 2021 (211)  
 SVHC > Threshold:  
 Cadmium oxide (7.95% in Contact)  
**Article Safe Usage Statements:**  
 Use personal protective equipment as required. Do not eat, drink or smoke when using this product. Recycle if possible and dispose of the article by following all applicable governmental regulations relevant to your geographic location.

Halogen Content Not Low Halogen - contains Br or Cl > 900 ppm.

Solder Process Capability Not applicable for solder process capability


#### Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

## Compatible Parts



## Also in the Series | Potter & Brumfield W57



## Customers Also Bought





## Documents

### CAD Files

Customer View Model

[ENG\\_CVM\\_1-1423364-2\\_1108.3d\\_igs.zip](#)

English

Customer View Model

[ENG\\_CVM\\_1-1423364-2\\_1108.3d\\_stp.zip](#)

English

Customer View Model

[ENG\\_CVM\\_1-1423364-2\\_1108.2d\\_dxf.zip](#)

English

### 3D PDF

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

### Datasheets & Catalog Pages

[W57 Compact Push To Reset Only Thermal Circuit Breaker](#)

English

[Industrial Relays Quick Reference Guide](#)

English

[Industrial Relays Quick Reference Guide](#)

Japanese

[Industrial Relays Quick Reference Guide](#)

### Product Environmental Compliance

[Product Compliance](#)

English

[Product Compliance](#)

English