

TDS10SGRNTU04

✓ ACTIVE

Alcoswitch | Alcoswitch DIP TDS


TE Internal #: 1-2319747-0

Alcoswitch DIP TDS, DIP & SIP Switches, Switch, Gold, Black DIP & SIP Switch Housing Color, High Temperature Nylon, 10 Switch

[View on TE.com >](#)



Relays, Contactors & Switches > Switches > DIP & SIP Switches



DIP & SIP Switch Product Type: **Switch**
DIP & SIP Switch Contact Mating Area Plating Material: **Gold**
DIP & SIP Switch Housing Color: **Black**
DIP & SIP Switch Housing Material: **High Temperature Nylon**
Sealed DIP & SIP Switch: **No**

Features

Product Type Features

DIP & SIP Switch Product Type	Switch
Sealed DIP & SIP Switch	No
DIP & SIP Switch Type	DIP Switch
Actuator Style	Slide

Configuration Features

Number of Positions	10
Number of Switches	10
Configuration (Pole-Throw)	Single Pole - Three Throw

Electrical Characteristics

DIP & SIP Switch Voltage Rating	24 VDC
---------------------------------	--------

Body Features

Actuator Color	White
----------------	-------

Contact Features

Shunt Type	DIP
------------	-----



DIP & SIP Switch Contact Mating Area Plating Material	Gold
DIP & SIP Switch Contact Current Rating	.025 A
Contact Base Material	Copper Alloy

Mechanical Attachment

Mounting Angle	Vertical
DIP & SIP Switch Mounting Type	Surface Mount

Housing Features

DIP & SIP Switch Housing Color	Black
DIP & SIP Switch Housing Material	High Temperature Nylon
DIP & SIP Switch Centerline	2.54 mm[.1 in]

Dimensions

Length	26.56 mm[1.046 in]
Height	4.1 mm[.161 in]

Usage Conditions

Operating Temperature Range	-20 – 85 °C
-----------------------------	-------------

Packaging Features

Packaging Method	Tube
Packaging Quantity	34

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2021 (211) Candidate List Declared Against: JAN 2021 (211) Does not contain REACH SVHC
Halogen Content	Not Yet Reviewed for halogen content
Solder Process Capability	Not reviewed for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as



EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # 1-2319747-6
TRI-STATE DIP 4P G RAISED T&R



TE Part # 2319747-1
TRI-STATE DIP 4P G RAISED TUBE



TE Part # 2-2319747-1
TRI-STATE DIP 4P G RECESS T&R




TE Part # 2-2319747-6
TRI-STATE DIP 4P G RECESS SEAL T&R



TE Part # 1-2319747-1
TRI-STATE DIP 4P G RECESS SEAL TUBE

Also in the Series | Alcoswitch DIP TDS



DIP & SIP Switches(30)

Customers Also Bought







TE Part #3-5332070-5
Mini Spring Socket Knockout Bottom, 6.5A



TE Part #2-2176050-5
Thick Film Resistor: Current Sense




TE Part #2198230-3
SFP+ Enhanced 1x2, Networking Heatsink



TE Part #176394-2
CT BOX HDR ASSY H 2P GOLD



TE Part #3-2176347-7
CRGCQ 2010 10K 1%



TE Part #2-2176391-1
RQ 1206 20K 0.1% 10PPM 5K RL



TE Part #212059-1
RECPT ASSY,SZ 3,AMPLIMITE COAX



TE Part #2337822-1
DISCR.ETH.MAG. 10/100 SINGLE SMT



TE Part #BM3041-000
CPGI-B-106-2503/1503-5



TE Part #2101579-2
DUST CAP,RCPT,Sz105,F SERIES

Documents

Product Drawings

TRI-STATE DIP 10P G RECESS TUBE

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_1-2319747-0_A.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_1-2319747-0_A.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_1-2319747-0_A.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages



SWITCHES_CORE_PROGRAM_CATALOG

English