



Relays, Contactors & Switches > Switches > Tactile Switches



Actuator Style: **Rectangular**
Operating Function: **Off (On)**
Contact Base Material: **Brass**
Switch Contact Plating Material: **Silver**
Dust Proof: **No**

Features

Product Type Features

Product Type	Switch
Leg Style	Gull Wing
Illuminated	No
Actuator Style	Rectangular
Dust Proof	No

Configuration Features

Tactile Feel	Yes
ESD Grounding Terminal	Without
Ganged	With
Tactile	Yes
Snap Action	Without
Operating Function	Off (On)
Support Bracket	Without
Configuration (Pole-Throw)	Single Pole - Single Throw
Number of Actuators	1

Electrical Characteristics

Tactile Switch Voltage Rating	24 VDC
-------------------------------	--------

Body Features

--	--



Cover Material	Stainless Steel
Case Color	Brown
Actuator Force	180 g[6.349 oz]
Case Material	Polyester
Bushing Style	Unthreaded
Actuator Profile	Extended
Actuator Material	Polyamide
Actuator Color	Black

Contact Features

Contact Base Material	Brass
Switch Contact Plating Material	Silver
Tactile Switch Contact Current Rating	50 mA

Termination Features

Termination Type	Printed Circuit Board
------------------	-----------------------

Mechanical Attachment

Tactile Switch Mounting Type	Surface Mount
Tactile Switch Mounting Angle	Vertical

Housing Features

Low Profile	With
Process Sealed	No

Dimensions

Actuator Length	1.07 mm[.042 in]
Button Width	2.99 mm[.118 in]
	.18 in

Usage Conditions

Temperature Rating	Standard °C
--------------------	-------------

Packaging Features

Packaging Method	Tape & Reel
------------------	-------------

Other

Comment	(On) indicates momentary position.
---------	------------------------------------

Product Compliance



For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2021 (211) Candidate List Declared Against: JAN 2021 (211) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Reflow solder capable to 260°C

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # 1825910-6
FSM4JH=6MM TACT SWITCH, HIGH TEMP




TE Part # 2-1825910-7
FSM14JH=6MM TACT SWITCH, HIGH TEMP



TE Part # 4-1437565-2
FSM4JSMATR=TACT SWITCH 6X6MIL



TE Part # 3-1437565-0
FSM2JSMATR=ON T/R



TE Part # 2-1977223-8
FSM14JSMAS=6MM TACT SWITCH, SMT 160gf



Customers Also Bought

TE Part #1571983-5
GDH04STR04=DIP SWITCH

TE Part #1-1879417-9
CPF 0603 1M0 0.1% 25PPM 1K RL

TE Part #1625854-2
0805 PROBE PAD

TE Part #1625854-3
0603 PROBE PAD

TE Part #1571983-4
GDH04S04=DIP SWITCH

TE Part #1437566-3
FSMSM=3.5X6 SMT TACT

TE Part #1-2176316-8
MELF SMA_A 2K7 0.1% 15PPM 0207 1W

TE Part #1565917-4
DDR2 SO DIMM Sockets

TE Part #1-2176367-6
RQ 0603 6K65 0.1% 10PPM 1K RL

TE Part #HDP24-24-91PE-L015
DEUTSCH HDP20 HOUSINGS

Documents

Product Drawings
FSMSMTR=TACT SWITCH

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_1437566-4_C_c-1437566-4-c.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_1437566-4_C_c-1437566-4-c.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_1437566-4_C_c-1437566-4-c.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.



Datasheets & Catalog Pages

Products for Mobile Equipment

English

SWITCHES_CORE_PROGRAM_CATALOG

English

Product Environmental Compliance

MD_1437566-4_09212018016_dmtec

English

MD_1437566-4_09212018016_dmtec

English