




Relays, Contactors & Switches > Switches > Rotary Switches



Number of Rotary Switch Positions: 10

Actuator Style: Flush

Switch Style: Rotary

Rotary Switch Type: Rotary DIP

Number of Switches: 10

Features

Product Type Features

Removable Tape Seal	Without
Product Type	Switch
Illuminated	No
Actuator Style	Flush
Switch Style	Rotary
Rotary Switch Type	Rotary DIP
Sealed Rotary Switch	Yes
Code Type	BCD Complement

Configuration Features

Number of Rotary Switch Positions	10
Number of Switches	10

Electrical Characteristics

Rotary Switch Voltage Rating	20 VAC
------------------------------	--------

Contact Features

Solder Tail Contact Plating	Gold Flash over Nickel
Rotary Switch Contact Current Rating	.4 A
Rotary Switch Contact Mating Area Plating Material	Gold Flash
Contact Base Material	Copper Alloy



Mechanical Attachment

Rotary Switch Mounting Type	Through Hole
Rotary Switch Mounting Angle	Vertical

Housing Features

Centerline	2.54 mm[.1 in]
Rotary Switch Housing Material	Thermoplastic

Usage Conditions

Oil-Tight	No
-----------	----

Industry Standards

UL Flammability Rating	UL 94V-0
------------------------	----------

Packaging Features

Packaging Method	Tube
------------------	------

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2021 (211) Candidate List Declared Against: JAN 2021 (211) Does not contain REACH SVHC
Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Wave solder capable to 265°C

Product Compliance Disclaimer


This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>



Compatible Parts

 TE Part # 1-1825007-6 DRD16E04=ROT DIP,16P	 TE Part # 1825007-6 DRD10E04=ROT DIP,10P	 TE Part # 1-1825007-1 DRD16CE04=ROT DIP,16P	 TE Part # 2-1825007-0 DRD16SETR04=ROT DIP,16P,SMT
 TE Part # 1-1825007-0 DRD10SETR04=ROT DIP,10P,SMT	 TE Part # 1825007-8 DRD10SE04=ROT DIP,10P,SMT	 TE Part # 1-1825007-3 DRD16CSE04=ROT DIP,16P,SMT	 TE Part # 1-1825007-8 DRD16SE04=ROT DIP,16P,SMT
 TE Part # 1-1825007-9 DRD16SAETR04=ROT DIP,16P,SMT	 TE Part # 1825007-9 DRD10SAETR04=ROT DIP,10P,SMT		

Also in the Series | Alcoswitch DIP

 DIP & SIP Switches(291)	 Rotary Switches(34)	 Switch Boots & Accessories(1)
--	---	--

Also in the Series | Alcoswitch Rotary DIP DRD



Rotary Switches(13)

Customers Also Bought



TE Part #1658615-2
IDC D-Sub: Plug Assembly, Low Profile, Signal, 2.77 mm




TE Part #1-6609028-0
CORCOM K SERIES SINGLE PHASE FILTERS




TE Part #8-1879233-4
SMD Power Resistor: 7 Watt, 200-2M Ohm




TE Part #1734709-4
AMP HPI 1.0MM HEADERS



TE Part #1-66105-8
III+ SKT,24-20,30AU/FL,SMPACK



TE Part #1-338088-6
8/8 INV.MOD.JACK



TE Part #1-66103-7
III+ PIN,24-20,15AU/FL,SMPACK



TE Part #1-1825007-1
DRD16CE04=ROT DIP,16P



TE Part #1825011-2
ASF22G04=DPDT AUTOSLIDE



TE Part #1-1971817-0
10P,RAST 2.5 Tab Header,Ex- Locking, THV

Documents

Product Drawings
DRD10CE04=ROT DIP,10P
English

CAD Files
3D PDF
3D
Customer View Model
ENG_CVM_CVM_1825007-1_A_c-1825007-1-a.2d_dxf.zip



English

Customer View Model

[ENG_CVM_CVM_1825007-1_A_c-1825007-1-a.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_1825007-1_A_c-1825007-1-a.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

[SWITCHES_CORE_PROGRAM_CATALOG](#)

English