



Relays, Contactors & Switches > Switches > Push Button Switches



Configuration (Pole-Throw): **Single Pole - Single Throw**

Push Button Switch Product Type: **Vandal Resistant**

Number of Actuators: **Single**

Actuator Profile: **Flush**

Bushing Style: **Threaded**

Features

Product Type Features

Switch Type	Pushbutton
Dust Proof	Yes
Push Button Switch Product Type	Vandal Resistant
Illuminated	Yes
Actuator Style	Round

Configuration Features

ESD Grounding Terminal	Without
Detent Style	Audible
Configuration (Pole-Throw)	Single Pole - Single Throw
Number of Actuators	Single
Snap Action	Without
Support Bracket	Without
Tactile	No
Operating Function	Momentary

Electrical Characteristics

Push Button Switch Voltage Rating	250 VAC
-----------------------------------	---------

Body Features

Case Material	PBT
---------------	-----



Actuator Profile	Flush
Bushing Style	Threaded

Contact Features

Push Button Switch Contact Current Rating	5 A
Switch Contact Plating Material	Silver

Termination Features

Termination Type	Wire Lugs
------------------	-----------

Mechanical Attachment

Mounting Angle	Vertical
Push Button Switch Mounting Type	Panel

Housing Features

Process Sealed	Yes
----------------	-----

Dimensions

	22 in
--	-------

Industry Standards

IP Rating	IP67
-----------	------

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant with Exemptions
EU ELV Directive 2000/53/EC	Compliant with Exemptions
China RoHS 2 Directive MIIT Order No 32, 2016	Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2021 (211) Candidate List Declared Against: JAN 2021 (211) SVHC > Threshold: Pb (3.7% in Component Part) Article Safe Usage Statements: Do not eat, drink or smoke when using this product. Wash thoroughly after handling. Recycle if possible and dispose of the article by following all applicable governmental regulations relevant to your geographic location.
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer



This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

 TE Part # 2213772-1 AV22 SPM 5A MOVE RING LED WHITE 12V	 TE Part # 2213772-7 AV22 SPM 5A MOVE RING LED RED 24V	 TE Part # 1-2213772-1 AV22 SPM 5A MOVE RING LED YELLOW 24V	 TE Part # 1-2213772-5 AV22 SPM 5A MOVE RING LED GREEN 24V
 TE Part # 1-2213772-7 AV22 SPM 5A MOVE RING LED BLUE 12V	 TE Part # 1-2213772-9 AV22 SPM 5A MOVE RING LED BLUE 24V	 TE Part # 2213771-3 AV22 SPL 5A NO LED	 TE Part # 2-2213772-1 AV22 SPL 5A MOVE RING LED WHITE 12V
 TE Part # 2-2213772-3 AV22 SPL 5A MOVE RING LED WHITE 24V	 TE Part # 2-2213772-5 AV22 SPL 5A MOVE RING LED RED 12V	 TE Part # 2-2213772-7 AV22 SPL 5A MOVE RING LED RED 24V	 TE Part # 3-2213772-1 AV22 SPL 5A MOVE RING LED YELLOW 24V
 TE Part # 3-2213772-9 AV22 SPL 5A MOVE RING LED BLUE 24V	 TE Part # 2213771-5 AV22 DPM 5A NO LED	 TE Part # 4-2213772-3 AV22 DPM 5A MOVE RING LED WHITE 24V	 TE Part # 4-2213772-5 AV22 DPM 5A MOVE RING LED RED 12V





TE Part # 5-2213772-1
AV22 DPM 5A MOVE RING LED
YELLOW 24V



TE Part # 5-2213772-7
AV22 DPM 5A MOVE RING LED BLUE
12V



TE Part # 5-2213772-9
AV22 DPM 5A MOVE RING LED BLUE
24V



TE Part # 2213771-7
AV22 DPL 5A NO LED

Also in the Series

Alcoswitch AV22



Push Button Switches(124)

Customers Also Bought



TE Part #1-2213764-3
AV19 SPM 5A FIX RING LED GREEN
12V




TE Part #1-2213772-5
AV22 SPM 5A MOVE RING LED
GREEN 24V



TE Part #1-2213772-7
AV22 SPM 5A MOVE RING LED BLUE
12V




TE Part #1-2213772-9
AV22 SPM 5A MOVE RING LED BLUE
24V




TE Part #1-2317656-9
AV25 SPL 3A MOVING RING BLUE 12V



TE Part #1-2176411-1
1/2W SM M/OX 5% 30K




TE Part #ZPF000000000137792
PANEL MOUNTING CLIP



TE Part #11029206-00
PIEZO FILM SHEETS



TE Part #1-2213772-3
AV22 SPM 5A MOVE RING LED
GREEN 12V



TE Part #1879744-1
RP 1J 51R1 0.1% 15PPM CUT LENGTH



Documents

Product Drawings

AV22 SPM 5A MOVE RING LED RED 12V

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_2213772-5_A.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_2213772-5_A.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_2213772-5_A.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

ALCOSWITCH Anti-Vandal Switch flyer

English

Agency Approvals

UL Report

English