FSMIJ62BB04 ✔ ACTIVE

Alcoswitch | Alcoswitch FSMIJ

TE Internal #: 2-2213818-5

Alcoswitch FSMIJ, Tactile Switches, Rectangular Actuator Style, Operating Function Off (On), Brass, Silver, 50mA Tactile Switch Contact Current Rating

View on TE.com >

Relays, Contactors & Switches > Switches > Tactile Switches



Actuator Style: **Rectangular**

Operating Function: **Off (On)**

Contact Base Material: **Brass**

Switch Contact Plating Material: **Silver**

Dust Proof: **No**

Features

Product Type Features

Illuminated	With
Actuator Style	Rectangular
Dust Proof	No

Configuration Features

Operating Function	Off (On)
Configuration (Pole-Throw)	Single Pole - Single Throw
Number of Actuators	1

Body Features

Actuator Color	Brown

Contact Features

Contact Base Material	Brass
Switch Contact Plating Material	Silver
Tactile Switch Contact Current Rating	50 mA

Mechanical Attachment

Tactile Switch Mounting Type	Through Hole
Tactile Switch Mounting Angle	Vertical

Housing Features

Process Sealed	No

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2021 (211) Candidate List Declared Against: JUL 2019 (201) SVHC > Threshold: Not Yet Reviewed
Halogen Content	Not Yet Reviewed for halogen content
Solder Process Capability	Wave solder capable to 265°C

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: https://echa.europa.eu/guidance-documents/guidance-on-reach

Compatible Parts



TE Part # 5-2213819-3
6X6 ILL TACT SMT 520GF LI SOFT ORANGE



TE Part # 2-2213819-9
6X6 ILL TACT SMT 160GF HI SOFT ORANGE



TE Part # 4-2213819-5
6X6 ILL TACT SMT 260GF HI SOFT ORANGE



TE Part # 4-2213819-8
6X6 ILL TACT SMT 260GF HI COLD WHITE



TE Part # 2-2213819-3
6X6 ILL TACT SMT 160GF LI RED

Also in the Series | Alcoswitch FSMIJ



Tactile Switches(128)

Customers Also Bought



TE Part #0462-209-16141
DEUTSCH SOLID CONTACTS




TE Part #1-1775470-3
AMP HPI 2.0MM HEADERS



TE Part #114017-ZZ
DEUTSCH SEALING PLUGS



TE Part #1-480698-0
02P UMNL PLUG HSG NATL



TE Part #1-2314826-6
16P,2MM,B-B,REC,DRVT,2.7,0.76AU, TB,W/CAP



TE Part #ZPF000000000018991
FDBA 54-20-16 PN-K 090



TE Part #1-2319747-5
TRI-STATE DIP 10P G RECESS SEAL TUBE

Documents

Product Drawings

6X6 ILL TACT THT 160GF HI BLUE

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_2-2213818-5_A.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_2-2213818-5_A.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_2-2213818-5_A.3d_stp.zip

English

By downloading the CAD file I accept and agree to the **Terms and Conditions** of use.

Datasheets & Catalog Pages

SWITCHES_CORE_PROGRAM_CATALOG

English