



Relays, Contactors & Switches > Switches > Push Button Switches



Push Button Switch Product Type: **Switch**

Number of Actuators: **Single**

Illuminated: **Yes**

Process Sealed: **No**

Snap Action: **With**

Features

Product Type Features

Switch Type	Pushbutton
Dust Proof	No
Push Button Switch Product Type	Switch
Illuminated	Yes
Actuator Style	Rectangular

Configuration Features

Ganged	No
Panel Cutout Size	16 (Diameter) mm
Number of Actuators	Single
Snap Action	With
Tactile	Yes
Operating Function	Push-On/Push-Off

Electrical Characteristics

Push Button Switch Voltage Rating	20 VDC, 24 VDC
Push Button Switch Power Rating	.4

Body Features

Seal Type	IP65
-----------	------

Contact Features



Type of Contact	1 NO & 1 NC
Contact Base Material	Copper Alloy
Push Button Switch Contact Current Rating	5 A
Switch Contact Plating Material	Gold

Mechanical Attachment

Mounting Angle	Vertical
Push Button Switch Mounting Type	Panel

Housing Features

Low Profile	No
Process Sealed	No

Dimensions

Button Width	15 mm[.59 in]
--------------	---------------

Usage Conditions

Oil-Tight	No
-----------	----

Operation/Application

For Use With	Lens Model 64T(*) (where * equals (2) Red, (3) Orange, (4) Yellow, (5) Green, (6) Blue, or (9) White., T1 3/4 midget flanged base lamps.
--------------	--

Other

Comment	Order Lamp Separately., Order Lens Set Separately.
---------	--

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2021 (211) Candidate List Declared Against: JAN 2021 (211) Does not contain REACH SVHC
Halogen Content	Not Yet Reviewed for halogen content
Solder Process Capability	Not applicable for solder process capability



Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # 3-1437569-5
164TL22=RECT MOM ILLUM PB 2NO&



TE Part # 1-1437569-2
164J2A22=2-POS KEYLK MAINT KYP



TE Part # 1437569-2
164EL11=RND MOM ILL PB 1NO&INC



TE Part # 2-1437569-5
164SL11=SQ MOM ILL PB 1NO&1NC



TE Part # 5-1437569-8
165TL533=OILTIGHT RECT MAINT I

Also in the Series | Alcoswitch Command



Keylock Switches(3)



Push Button Switches(13)



Rotary Switches(3)



Switch Boots & Accessories(17)

Customers Also Bought



TE Part #206044-1
CPC SERIES 6

TE Part #2-6609037-6
CORCOM EP SERIES SINGLE PHASE FILTERS

TE Part #1757819-6
AMPLIMITE,ASY,PLUG,STD,109,ZN,1,CT

TE Part #2-1419106-1
27E489=SOCKET,K10,8,QC.187,NYL

TE Part #2-103648-4
25 MTE RCPT HSG SR RIB .100CL

TE Part #1676913-9
YR1 0.1% 1K24

TE Part #1546306-8
8P .374" DR BARRIER STRIP

TE Part #174414-000
SO63-2-55-20-90

TE Part #103322-7
14 MODII HDR DRST B/A .100CL

TE Part #965005-000
CE-12-00300-MAIN-RPAIR-FX

Documents

Product Drawings

164TL511=RECT PP ILL PB INO&IN

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_3-1437569-8_A.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_3-1437569-8_A.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_3-1437569-8_A.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages



SWITCHES_CORE_PROGRAM_CATALOG

English