

W67-X2Q110-15 ✓ ACTIVE

Potter & Brumfield | Potter & Brumfield W6


TE Internal #: 4-1393252-2

Potter & Brumfield W6, Circuit Breakers, Magnetic, Series Trip, White Toggle Color, 415/240VAC Voltage Rating AC, 15A Circuit Breaker Current Rating

[View on TE.com >](#)



Relays, Contactors & Switches > Circuit Breakers



Circuit Breaker Type: **Magnetic**

Circuit Function: **Series Trip**

Illuminated: **No**

Toggle Color: **White**

Voltage Rating AC: **415/240 VAC**

Features

Product Type Features

Illumination Type	No Light
Product Type	Circuit Breaker
Actuator Type	Toggle
Circuit Breaker Type	Magnetic
Illuminated	No
Toggle Color	White

Configuration Features

	.75 x 1.66 in
Earthing Switch	Without
Circuit Function	Series Trip

Electrical Characteristics

Voltage Rating AC	415/240 VAC
Circuit Breaker Current Rating	15 A
Interrupt Capacity	5000A @ 277VAC

Contact Features

Pole Configuration	1
Trip Time at 200%	9 – 100 seconds

Termination Features



Circuit Breaker Termination Type	6.35 [.25] Straight Quick Connect Tab
----------------------------------	---------------------------------------

Mechanical Attachment

Series/Mounting Option	W6 (6-32 Mounting Threads)
------------------------	----------------------------

Mounting Options	6-32 Mounting Threads
------------------	-----------------------

Circuit Breaker Mounting Type	Panel Mount
-------------------------------	-------------

Dimensions

	.047 – .11 in
--	---------------

Circuit Breaker Size	50.8 mm[2 in]
----------------------	---------------

Identification Marking

Stamped Marking Type	International I/O
----------------------	-------------------

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
------------------------------	-----------

EU ELV Directive 2000/53/EC	Not Compliant
-----------------------------	---------------

China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
---	---

EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2021 (211) Candidate List Declared Against: JAN 2020 (205) SVHC > Threshold: Not Yet Reviewed
--	---

Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
-----------------	---

Solder Process Capability	Not applicable for solder process capability
---------------------------	--

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # 5-1393252-6
W67-X2Q12-15=M6/M7/M9/W6/W7



TE Part # 175022-1
250 PL EX REC. 18-14AWG PTBR



TE Part # 6-1393252-7
W67-X2Q13-15=M6/M7/M9/W6/W7




TE Part # 8-1393252-2
W67-X2Q52-15=M6/M7/M9/W6/W7



TE Part # 9-1393252-6
W67-X2S12-15=M6/M7/M9/W6/W7

Also in the Series | Potter & Brumfield W6



Circuit Breakers(71)

Customers Also Bought



TE Part #1-6609027-4
CORCOM K SERIES SINGLE PHASE FILTERS



TE Part #1734035-2
MINI USB, TYPE B, R/A, SMT



TE Part #1-1879355-7
RR03 5% 20K AMMO



TE Part #1218408-4
AMPLIMITE,ASY,RCPT,RTANG,109,4




TE Part #1-1393254-7
W91-X1110-15=M6/M7/M9/W6/W7




TE Part #DTS20W11-35PA
D38999: Square Flange, 11-35 insert




TE Part #2-1393253-3
W68-X2Q110-25V=M6/M7/M9/W6/W7



TE Part #0934-201-1458
SHL PLUG ASSY



TE Part #0619-5-1178
DBA R SNAP



TE Part #106794-03
INS PIN ASSY

Documents

CAD Files

Customer View Model

[ENG_CVM_4-1393252-2_1106.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_4-1393252-2_1106.3d_stp.zip](#)

English

Customer View Model

[ENG_CVM_4-1393252-2_1106.2d_dxf.zip](#)

English

3D PDF

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

W6/W9 Magnetic Hydraulic Circuit Breaker

English

Industrial Relays Quick Reference Guide

English

Industrial Relays Quick Reference Guide

Japanese

Industrial Relays Quick Reference Guide