



All DIP Socket: Standard, Stamped & Formed, Open, Gold (4)

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2021 (211) Candidate List Declared Against: JAN 2021 (211) Does not contain REACH SVHC
Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Wave solder capable to 265°C

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Customers Also Bought






TE Part #1-1393154-2
PT570024



TE Part #1393194-9
T77S1D10-12




TE Part #1986242-3
Power Connector, 15.0mm, Green, 3
posn



TE Part #9-2176391-9
RQ 1206 130K 0.1% 10PPM 5K RL



TE Part #2-1761679-5
IDC LOW PRO HDR 14P VERT BLUE



TE Part #2-1879639-8
H4P 36R5 0.5% 50PPM



TE Part #1-2199299-5
DIP Socket: Standard, Stamped &
Formed, Open, Tin



TE Part #1-1761685-1
IDC LOW PRO HDR 34P VERT SHT LAT



TE Part #103328-9
18 MODII HDR DRST B/A .100CL



TE Part #1-1437667-4
4DB-P107-07=4DB ASSEMBLY

Documents

Product Drawings

818-AG11D-ES-LF=800 DIP,AU/SN

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_4-1571552-5_E.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_4-1571552-5_E.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_4-1571552-5_E.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages



DIP Sockets Quick Reference Guide (EN)

English