

45433 ✓ ACTIVE

AMP

TE Internal #: 45433

Portable Crimp Tools, Premium Crimp Tooling, Removable /Interchangeable, MIL Spec / TE Product Specification (114-), Manual / Battery / Hydraulic

[View on TE.com >](#)



Application Tooling > Portable Crimp Tools



Tool Grade: Premium Crimp Tooling

Die Sets Type: Removable/Interchangeable

Specification Type: MIL Spec, TE Product Specification (114-)

TE Certification: Upon Request for Fee

Power Technology Type: Battery, Hydraulic, Manual

## Features

### Other

Crimp Form-Wire Barrel Type	Closed Barrel - W Crimp
Tool Grade	Premium Crimp Tooling
Die Sets Type	Removable/Interchangeable
Specification Type	MIL Spec, TE Product Specification (114-)
TE Certification	Upon Request for Fee
Power Technology Type	Battery, Hydraulic, Manual
Tooling Type	Die Assembly

## Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Out of Scope
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2021 (211) Candidate List Declared Against: JUL 2017 (174) SVHC > Threshold: Not Yet Reviewed
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per

homogenous material. Also BFR/CFR/PVC Free

Solder Process Capability

Not reviewed for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

### Compatible Parts



TE Part # 330301  
TERMINAL,SOLIS R 2 10



TE Part # 320138  
TERMINAL,SOLIS R 2 1/4



TE Part # 320754  
TERMINAL,SOLIS R 2 5/8




TE Part # 35184  
TERMINAL,SOLIS R 2 3/8



TE Part # 35185  
TERMINAL,SOLIS R 2 1/2



TE Part # 320383  
TERMINAL,SOLIS R 2 1/4




TE Part # 323291  
TERMINAL,SOLIS R 2 1/2



TE Part # 2-322870-2  
STRATO-THERM, HR 2 5/16 NIPL



TE Part # 321600  
TERMINAL,SOLIS R 2 3/8



TE Part # 320741  
TERMINAL,SOLIS R 2 7/16



TE Part # 322870  
TERMINAL,SOLIS R 2 5/16



TE Part # 8-322870-3  
TERMINAL,SOLIS R 2 5/16





TE Part # 130558  
TERMINAL,SOLIS R 2 10MM



TE Part # 35189  
SPLICE,SOLIS BUTT 2




TE Part # 320755  
TERMINAL,SOLIS R 2 3/4



TE Part # 323177  
STRATO-THERM, HR 2 3/8 NIPL



TE Part # 35183  
TERMINAL,SOLIS R 2 5/16



TE Part # 35187  
SPLICE,SOLIS PARA 2



TE Part # 330301-3  
TERMINAL,SOLIS, R, 2, M5



TE Part # 1752868-1  
HYP10 12-350MCM 18T HEAD

### Customers Also Bought



TE Part #1662-213-2031  
CONT SOC ASSY



TE Part #1901611-1  
CCII PIDG STRATO 24-20 ASSY



TE Part #8-240651-2  
BLADE, SLUG



TE Part #2150049-2  
OCEAN-2.0-APPLICATOR-E-062F090FA




TE Part #2151731-2  
OCEAN-2.0-APPLICATOR-S-100F130OA




TE Part #2304643-2  
38POS, HYBRID, REC HSG ASSY, SLD




TE Part #3-568176-1  
CRIMPER, WIRE



TE Part #21045-8  
RING, RETAINING, EXT CRESCENT



TE Part #300042  
RETAINING PIN



TE Part #300100  
CUP PACKING

### Documents



### Datasheets & Catalog Pages

[AT-Hydraulic Crimp Tooling Solutions-1654519](#)

English

[Crimp Term Whitepaper-Use the Right Tool 1-1773953-1](#)

English

[Bottoming Dies](#)

English

[CRIMPING WHERE FORM MEETS FUNCTION](#)

English

---

### Instruction Sheets

[Instruction Sheet \(U.S.\)](#)

English