



Application Tooling > Portable Crimp Tools



Tool Grade: **Premium Crimp Tooling**

Die Sets Type: **Removable/Interchangeable**

Specification Type: **MIL Spec, TE Product Specification (114-)**

TE Certification: **Yes – Certificate Included**

Power Technology Type: **Battery, Hydraulic, Manual**

Features

Other

Crimp Form-Wire Barrel Type	Closed Barrel - W Crimp
Tool Grade	Premium Crimp Tooling
Die Sets Type	Removable/Interchangeable
Specification Type	MIL Spec, TE Product Specification (114-)
TE Certification	Yes – Certificate Included
Power Technology Type	Battery, Hydraulic, Manual
Tooling Type	Die Assembly

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Out of Scope
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2021 (211) Candidate List Declared Against: JUN 2018 (191) SVHC > Threshold: Not Yet Reviewed
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per



homogenous material. Also BFR/CFR/PVC Free

Solder Process Capability

Not reviewed for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # 322224
TERMINAL,SOLIS R 2/0 5/8



TE Part # 321873
BODY SOLIS RING 2/0 1/2



TE Part # 36921
TERMINAL,SOLIS R 2/0 1/4



TE Part # 321869
TERMINAL,SOLIS R 2/0 1/4



TE Part # 36923
TERMINAL,SOLIS R 2/0 3/8



TE Part # 36925
TERMINAL,SOLIS R 2/0 1/2



TE Part # 321872
TERMINAL,SOLIS R 2/0 7/16



TE Part # 321871
BODY SOLIS RING 2/0 3/8




TE Part # 132074-2
TERMINAL SOLISTRAND RING 2/0,



TE Part # 36948
SPLICE,SOLIS PARA 2/0



TE Part # 36958
SPLICE,SOLIS BUTT 2/0



TE Part # 321870
TERMINAL SOLIS R 2/0 5/16




TE Part # 36922
TERMINAL,SOLIS R 2/0 5/16



TE Part # 160001
TERM,SOLIS R 2/0 M10



TE Part # 322225
TERMINAL,SOLIS R 2/0 3/4



TE Part # 321871-2
STRATO-THERM, HR 2/0 3/8 NIPL



TE Part # 321873-2
STRATO-THERM, HR 2/0 1/2 NIPL



TE Part # 1752868-1
HYP10 12-350MCM 18T HEAD



TE Part # 69099
HYP8 12-350MCM 18T HEAD



TE Part # 2-525441-1
PLUG GAUGE, HANDTOOL

Customers Also Bought



TE Part #1662-213-2031
CONT SOC ASSY



TE Part #1986727-2
AMPOWER KNIFE DISCONNECT



TE Part #1804700-1
HYP10 110V HEAVY DUTY ELECTRIC PUMP



TE Part #2-33466-1
SOLISTRAND RING 6 5/16



TE Part #2150049-2
OCEAN-2.0-APPLICATOR-E-062F090FA



TE Part #2151731-2
OCEAN-2.0-APPLICATOR-S-100F1300A




TE Part #2304643-2
38POS,HYBRID,REC HSG ASSY,SLD



TE Part #3-568176-1
CRIMPER, WIRE



TE Part #ZPF000000000019085
FDBA 56-10-6 SN-K 090



TE Part #134755-2
TERMINAL STRATO-THERM 2 0

Documents



Datasheets & Catalog Pages

[AT-Hydraulic Crimp Tooling Solutions-1654519](#)

English

[Crimp Term Whitepaper-Use the Right Tool 1-1773953-1](#)

English

[Bottoming Dies](#)

English

[CRIMPING WHERE FORM MEETS FUNCTION](#)

English

Instruction Sheets

[Instruction Sheet \(U.S.\)](#)

English