




Raychem | Raychem CGPT

TE Internal #: 5575754001

Raychem CGPT, Heat Shrink Tubing, Black, Single Wall Type, 18 Expanded Inside Diameter (Min) .709 Expanded Inside Diameter (Min)

[View on TE.com >](#)

Heat Shrink Tubing > Single Wall CGPT Spool Heat Shrink Tubin



Primary Product Color: **Black**

Wall Type: **Single**

Expanded Inside Diameter (Min): **18 mm [ .709 in ]**

Recovered Inside Diameter (Max): **6 mm [ .236 in ]**

Shrink Ratio: **3:1**

[All Single Wall CGPT Spool Heat Shrink Tubin \(186\)](#)

## Features

### Product Type Features

Product Family	CGPT
Wall Type	Single

### Electrical Characteristics

Voltage (Max)	.6 kV
---------------	-------

### Body Features

Fluid Type	Gasoline, Hydraulic Fluid, Lubricating Oil
Primary Product Color	Black
Shrink Ratio	3:1
Primary Product Material	Irradiated Modified Polyolefin
Flexibility	Flexible

### Dimensions

Recovered Wall Thickness (Tolerance)	.15 mm[.006 in]
Recovered Wall Thickness (Nominal)	.85 mm[.033 in]
Expanded Inside Diameter (Min)	18 mm[.709 in]
Recovered Inside Diameter (Max)	6 mm[.236 in]
Heat Shrink Tubing Size Range	6 – 18 mm[.236 – .709 in]



### Usage Conditions

Fluid Resistance	Splash Protection
Shrink Temperature (Min)	80 °C
Heat Shrink Tubing Flammability	Flame-Retardant
Operating Temperature Range	-40 – 135 °C
Heat Shrink Tubing Resistance	Fluids, Mechanical Damage, Strain
Recovery Temperature	120 °C

### Product Availability

Applicable Region	Asia, EMEA
-------------------	------------

### Packaging Features

Packaging Method	Box
------------------	-----

### Other

Meets Low Outgassing Requirements	No
Product Source	Czech Republic

### Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2021 (211) Candidate List Declared Against: JAN 2021 (211) Does not contain REACH SVHC
Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Not applicable for solder process capability

#### Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides

on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

## Also in the Series | Raychem CGPT



Heat Shrink Tubing(316)



Power Cable Tubing & Accessories(93)

## Customers Also Bought




TE Part #1-1438608-5  
MQS, CONNECTOR HOUSING



TE Part #144617-1  
TIMER, RECEPTACLE AND TAB



TE Part #1-2112891-2  
AMP MCP, UNSEALED CONNECTOR HOUSING



TE Part #1-1338690-2  
ANVIL, COMBINATION .055




TE Part #1-562108-5  
CRIMPER WIRE



TE Part #1379096-2  
COV+LEV MQS 12W 90DEG BLU




TE Part #1544980-1  
TAB HOUSING, 8MM NG1 PLUS, 2 WAY



TE Part #154740-1  
PIN .175 DIA REC 20-16AWG PB WAY



TE Part #CH02996001  
QSZH-125-NR3-65MM



TE Part #1333204-6  
ANVIL, COMBINATION .080

## Documents

[Product Drawings](#)  
[CGPT-18/6-0-SP](#)

English



---

**Datasheets & Catalog Pages**

[Application Tooling for Raychem Heat Shrink Product](#)

English

[CGPT Pages from 9-1773447-9](#)

English

---

**Product Specifications**

[Quality Specification](#)

English