




Application Tooling > Portable Crimp Tools



Tool Grade: **Commercial Crimp Tooling**
Ratchet Configuration: **Operator Releasable & Adjustable**
Die Sets Type: **Removable/Interchangeable**
Specification Type: **TE Product Specification (114-)**
TE Certification: **Upon Request for Fee**

Features

Other

Crimp Form-Wire Barrel Type	Open Barrel - F Crimp
Tool Grade	Commercial Crimp Tooling
Ratchet Configuration	Operator Releasable & Adjustable
Die Sets Type	Removable/Interchangeable
Specification Type	TE Product Specification (114-)
TE Certification	Upon Request for Fee
Power Technology Type	Battery, Electric, Manual
Tooling Type	Standard Die Envelope (SDE) Die Set

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Out of Scope
EU ELV Directive 2000/53/EC	Out of Scope
China RoHS 2 Directive MIIT Order No 32, 2016	Not reviewed for China RoHS compliance
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2021 (211) Candidate List Declared Against: JAN 2021 (211) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per



homogenous material. Also BFR/CFR/PVC Free

Solder Process Capability

Not applicable for solder process capability







Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>


Compatible Parts

 TE Part # CAT-035-DCCSC20 D-Sub Conn Contacts: Socket, Phosphor Bronze, Signal, Size 20	 TE Part # CAT-035-DCCPB20 D-Sub Connector Contacts: Pin, Brass, Signal, Size 20	 TE Part # CAT-035-DCRSS203 D-Sub Crimp Recpt Signal 25 Posn, Socket Size 20, Shell Size 3	 TE Part # CAT-035-DCPPS201 D-Sub Crimp: Plug, Signal, 9 Posn, Pin Size 20, Shell Size 1
 TE Part # CAT-035-DCPPS202 D-Sub Crimp: Plug, Signal, 15 Posn, Pin Size 20, Shell Size 2	 TE Part # CAT-035-DCPPS203 D-Sub Crimp: Plug, Signal, 25 Posn, Pin Size 20, Shell Size 3	 TE Part # CAT-035-DCRSS201 D-Sub Crimp Recpt Signal 9 Posn, Socket Size 20, Shell Size 1	 TE Part # CAT-035-DCRSS202 D-Sub Crimp Recpt Signal 15 Posn, Socket Size 20, Shell Size 2
 TE Part # 2280380-1 KIT, BT, MICRO SDE, 110V	 TE Part # 2280380-2 KIT, BT, MICRO SDE, 220V	TE Part # 166051-8 WITH OPEN BARRELS	TE Part # 166052-8 20DF SOCKET CONTACT



 TE Part # 2-66505-7 20 DF SOCKET	 TE Part # 6-66504-9 20 DF SCKT CONT W/GAP	 TE Part # 6-66506-5 PIN CONT,SIZE 20 DF 20-24 AWG	 TE Part # 6-66507-5 HD 20 DF PIN PLTD
 TE Part # 66504-1 20 DF SCKT CONTACT	 TE Part # 66505-1 20 DF SCKT CONTACT	 TE Part # 66506-1 20 DF PIN CONT	 TE Part # 66507-1 20 DF PIN CONT

Customers Also Bought

 TE Part #207464-2 D-Sub Crimp: Plug, Signal, 25 Posn, Pin Size 20, Shell Size 3	 TE Part #207463-1 D-Sub Crimp Recpt Signal 25 Posn, Socket Size 20, Shell Size 3	 TE Part #205205-2 D-Sub Crimp Recpt Signal 15 Posn, Socket Size 20, Shell Size 2	 TE Part #T4032014041-000 M8 Panel Mount Solder Cups
 TE Part #205841-1 CPC RECPT ASSEMBLY SIZE 11-8	 TE Part #1757823-1 AMPLIMITE,ASY,PLUG,STD,90,ZN,1	 TE Part #1579007-9 EXTRACTION TOOL	 TE Part #1214310-1 LOCATOR ASSY
 TE Part #2085120-1 CONN SOCKET ASSY STRAIGHT SOLDER FLATPAQ	 TE Part #2085122-1 CONN SOCKET ASSY STRAIGHT SOLDER FLATPAQ		

Documents



Datasheets & Catalog Pages

1-1773865-2_1015_Commercial Manual Hand Tools

English

Crimp Term Whitepaper-Use the Right Tool 1-1773953-1

English

Bottoming Dies

English

CRIMPING WHERE FORM MEETS FUNCTION

English

Instruction Sheets

Instruction Sheet (U.S.)

English