

59250 ✓ ACTIVE

AMP

TE Internal #: 59250

Portable Crimp Tools, Premium Crimp Tooling, Not Releasable, Not Adjustable, Fixed In Tool, TE Product Specification (114-) / MIL Spec

[View on TE.com >](#)



Application Tooling > Portable Crimp Tools



Tool Grade: **Premium Crimp Tooling**

Ratchet Configuration: **Not Releasable, Not Adjustable**

Die Sets Type: **Fixed In Tool**

Specification Type: **MIL Spec, TE Product Specification (114-)**

TE Certification: **Yes – Certificate Included**

## Features

### Other

Crimp Form-Wire Barrel Type	Closed Barrel - Confined Crescent
Tool Grade	Premium Crimp Tooling
Ratchet Configuration	Not Releasable, Not Adjustable
Die Sets Type	Fixed In Tool
Specification Type	MIL Spec, TE Product Specification (114-)
TE Certification	Yes – Certificate Included
Power Technology Type	Battery, Manual
Tooling Type	T Head Hand Tool

## Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Out of Scope
EU ELV Directive 2000/53/EC	Out of Scope
China RoHS 2 Directive MIIT Order No 32, 2016	Not reviewed for China RoHS compliance
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2021 (211) Candidate List Declared Against: JAN 2019 (197) SVHC > Threshold: Not Yet Reviewed

Halogen Content

Not Yet Reviewed for halogen content


Solder Process Capability


Not applicable for solder process capability

## Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulations, TE's information on SVHC in articles for this part number is still based on the European Chemical Agency (ECHA) 'Guidance on requirements for substances in articles' (Version: 2, April 2011), applying the 0.1% weight on weight concentration threshold at the finished product level. TE is aware of the European Court of Justice ruling of September 10th, 2015 also known as O5A (Once An Article Always An Article) stating that, in case of 'complex object', the threshold for a SVHC must be applied to both the product as a whole and simultaneously to each of the articles forming part of its composition. TE has evaluated this ruling based on the new ECHA "Guidance on requirements for substances in articles" (June 2017, version 4.0) and will be updating its statements accordingly.

## Compatible Parts



TE Part # CAT-P592-R2456  
PIDG RECTANGULAR TONGUE  
TERMINALS




TE Part # 8-31880-1  
PIDG R 22-16 COMM 22-18 MIL 4




TE Part # 8-34148-1  
PG R 22-16 COMM 22-18 MIL 8



TE Part # 324227  
PG SHUR PLUG 16-14



TE Part # 66023-2  
TAB, PIDG TERMI-BK 22-16



TE Part # 34141  
PG R 22-16 COMM 22-18 MIL 4



TE Part # 31906  
TERMINAL, PIDG R 16-14 1/4



TE Part # 52950  
PG SPR SPD 22-16 COMM 22-18 MIL 8

### Customers Also Bought



TE Part #218208-002  
22759/34-16-9



TE Part #218204-001  
22759/34-20-9



TE Part #2560-201-2031L  
CONT PIN



TE Part #220015-1  
HHHT COAXIAL ASSY



TE Part #218203-002  
22759/34-22-9




TE Part #2560-215-1631L  
CONT PIN



TE Part #E99238-000  
HTCM-SCE-TP HIGH TEMPERATURE  
MARKERS



TE Part #169311-000  
55A1822-24-9/96-9CS2275



TE Part #1055451-1  
LOCATOR TOOL



TE Part #230287-3  
FIELD SERVICE INSERTION TOOL

### Documents



### Product Drawings

[T-HEAD PIDG 26-14 ASSY](#)

English

---

### Datasheets & Catalog Pages

[CERTI-CRIMPPII-Premium-August-1-1773864-7](#)

English

[PIDG TERMINALS & SPLICES Quick Reference Guide](#)

English

[Crimp Term Whitepaper-Use the Right Tool 1-1773953-1](#)

English

### Bottoming Dies

English

[CRIMPING WHERE FORM MEETS FUNCTION](#)

English

---

### Instruction Sheets

[Instruction Sheet \(U.S.\)](#)

English

[Instruction Sheet \(U.S.\)](#)

English