



TE Internal #: 605980-2
Fusion Tape, Fusion, Fusion Tape Tape Width 25.4 mm [1 in],
Fusion Tape Roll Length 30 ft [9.144 m], Black, Fusion Tape
Thickness .02 in [.51 mm]
[View on TE.com >](#)

Wire Protection & Management > Adhesives & Sealants > Fusion Tape



Tape Type: **Fusion**
Fusion Tape Tape Width: **25.4 mm [1 in]**
Fusion Tape Roll Length: **9.144 m [30 ft]**
Fusion Tape Color: **Black**
Fusion Tape Thickness: **.51 mm [.02 in]**

Features

Product Type Features

Product Type	Accessory
Tape Type	Fusion
Center Stripe	No

Body Features

Weight	47.8 g[.105 lb]
Material Features	Self-Amalgamating
Material	Polyisobutylene
Fusion Tape Color	Black

Dimensions

Fusion Tape Tape Width	25.4 mm[1 in]
Fusion Tape Thickness	.51 mm[.02 in]

Packaging Features

Packaging Quantity	1
Packaging Method	Roll
Fusion Tape Roll Length	9.144 m[30 ft]

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
------------------------------	-----------



EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2021 (211) Candidate List Declared Against: JAN 2021 (211) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # 608036-6
SILICONE FUSION TAPE, 1.25"X36'



TE Part # 604271-2
ELECTRICAL TAPE, PVC, BLACK

Customers Also Bought



TE Part #1658645-1
D-Sub Crimp: Plug, Signal, 9 Posn, Pin Size 20, Shell Size 1



TE Part #1658647-1
D-Sub Crimp: Plug, Signal, 15 Posn, Pin Size 20, Shell Size 2



TE Part #1658649-1
D-Sub Crimp Recept Signal 25 Posn, Socket Size 20, Shell Size 3



TE Part #1658675-1
D-Sub Crimp: Plug, Signal, 50 Posn, Pin Size 22, Shell Size 1



TE Part #1658646-1

D-Sub Crimp Recpt Signal 9 Posn, Socket Size 20, Shell Size 1

TE Part #2-31886-2

PIDG RING TONGUE TERMINALS

TE Part #1658537-1

D-Sub Conn Contacts: Socket, Phosphor Bronze, Signal, Size 20

TE Part #1757824-7

AMPLIMITE,ASY,RCPT,STD,90,ZN,1,CT

TE Part #1-1757824-1

AMPLIMITE,ASY,RCPT,STD,90,ZN,5,CT

TE Part #ZPF000000000202709

DMC-MR 30-23 SN

Documents

Product Drawings

FUSION TAPE, 1" X .020" X 30FT

English

Instruction Sheets

Instruction Sheet (U.S.)

English