



Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2021 (211) Candidate List Declared Against: JAN 2021 (211) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Wave solder capable to 265°C


Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Also in the Series | [Alcoswitch ADP](#)



Card Edge Connector Housings(4)








DIP & SIP Switches(8)



RJ45 Connectors(1)

Customers Also Bought

TE Part #1623734-6
Wirewound Resistor: Vertical MountTE Part #1-1879444-7
Wirewound Resistor: Mineral, 2.5 KwTE Part #9-1879627-5
H4P 82K 1% 100PPMTE Part #118982-1
KEYING PLUGTE Part #1546073-8
8 POS 5.08MM TERMI-BLOKTE Part #1546399-7
6PCR-21-006=#6 TRIBARRIERTE Part #2-2176404-5
3550 130K 1%TE Part #1393767-1
R10-E2P2-V185=R10TE Part #2314936-3
3P,2MM,B-B,REC,SRHZ,2.8,0.1AU,TRTE Part #3-1393767-9
R10-E2Z2-J1.0K=R10

Documents

Product Drawings

8080-1G36-LF=TRANSISTOR SOCKET AS

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_6-6437504-2_C.2d_dxf.zip



English

Customer View Model

[ENG_CVM_CVM_6-6437504-2_C.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_6-6437504-2_C.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.