



Application Tooling > Spare & Wear Tooling



Applicator & Product Style: **Heavy Duty Mini (HDM)**

Features

Other

Applicator & Product Style	Heavy Duty Mini (HDM)
----------------------------	-----------------------

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)


EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Out of Scope
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2021 (211) Candidate List Declared Against: JAN 2021 (211) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>



Compatible Parts


 TE Part # 2836135-2 OCEAN_2.0_APPLICATOR-S-033F055OA	 TE Part # 2836265-2 OC-AT-S-FA-116F232O-040-0612	 TE Part # 2151307-1 OCEAN_2.0_APPLICATOR-S-042F062O	 TE Part # 2-2151020-1 OCEAN_2.0_APPLICATOR-S-055F062O
 TE Part # 2-2151020-2 OCEAN_2.0_APPLICATOR-S-055F062O	 TE Part # 2-2151142-1 OCEAN_2.0_APPLICATOR-S-042F070F	 TE Part # 2-2151142-2 OCEAN_2.0_APPLICATOR-S-042F070F	 TE Part # 2-2151307-1 OCEAN_2.0_APPLICATOR-S-042F062O
 TE Part # 2-2151307-2 OCEAN_2.0_APPLICATOR-S-042F062OA	 TE Part # 2-2151432-1 OCEAN_2.0_APPLICATOR-S-055F062O	 TE Part # 2-2151432-2 OCEAN_2.0_APPLICATOR-S-055F062O	 TE Part # 2-2151638-1 OC-PA-S-FM-100F120F-094-1292
 TE Part # 2-2151638-2 OC-PA-S-FA-100F120F-094-1292	 TE Part # 2-2151710-1 OC-PA-S-FM-102F141F-030-0745	 TE Part # 2-2151710-2 OC-PA-S-FA-102F141F-030-0745	 TE Part # 2-2151711-2 OCEAN_2.0_Applicator-S-143F283O
 TE Part # 2-2151755-1 OC-PA-S-FM-055F055F-011-0577	 TE Part # 2-2151755-2 OC-PA-S-FA-055F055F-011-0577	 TE Part # 2-2151766-1 OC-PA-S-FM-042F062F-001-0138	 TE Part # 2-2151766-2 OC-PA-S-FA-042F062F-001-0138

Customers Also Bought





TE Part #207359-1
RECEPT HSG,3 POSN,METRIC



TE Part #1803095-3
FLOATING SHEAR, FRONT




TE Part #2119805-1
SHEAR HOLDER, FRONT, CUT



TE Part #2119806-1
INSERT, SHEAR



CRIMPER REPRESENTATION ONLY
TE Part #1803224-9
CRIMPER,WIRE F



TE Part #2-1633127-7
ANVIL, COMBINATION .042



TE Part #2119862-1
SHEAR HOLDER, REAR



TE Part #9-683454-2
CRIMPER, INSULATION "O"

TE Part #3-22280-3
SPRING,COMPRESSION

TE Part #1320920-1
SHEAR HOLDER, REAR

Documents

Datasheets & Catalog Pages
CRIMPING WHERE FORM MEETS FUNCTION
English

Instruction Sheets
Instruction Sheet (U.S.)
English