HT-SCE-1K-1/4-2.0-0 ✔ ACTIVE

TE Internal #: 769356-000

TE Internal Description: HT-SCE-1K-1/4-2.0-0

View on TE.com >



Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2021 (211) Candidate List Declared Against: JAN 2021 (211) Does not contain REACH SVHC
Halogen Content	Low Bromine/Chlorine - Br and Cl < 900 ppm per homogenous material. Also BFR /CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: https://echa.europa.eu/guidance-documents/guidance-on-reach

Compatible Parts




TE Part # 1-2186500-1
T3212-PRINTER



TE Part # 1-2186502-1
T3224-PRINTER



TE Part # 1-2186503-1
T3224-SWARE-PRINTER



TE Part # 154739-000
T300-RIBBON-WH-4HT

HT-SCE-1K-1/4-2.0-0




TE Part # CP8122-000
T6112DS-PRINTER



TE Part # 1-2186501-1
T3212-SWARE-PRINTER

Customers Also Bought



TE Part #408452-000
Bulbous Heat Shrink Boots: Lipped, Straight



TE Part #479613-000
Heat Shrink Boots: Non Lipped, Straight



TE Part #5039364006
Single Wall DR 25: Heat Shrink Tubing, 2:1 Shrink Ratio



TE Part #2209350001
HT-SCE HIGH TEMPERATURE SLEEVES



TE Part #3490750001
D-SCE FLUID RESISTANT SLEEVES



TE Part #ZPF000000000009012
983-6SE 24-30 P8 L

Documents

Product Drawings

HT-SCE-1K-1/4-2.0-0

English

Datasheets & Catalog Pages

HT-SCE Heat Shrinkable Sleeves

English

Product Specifications

Product Specification

English

Instruction Sheets

Instruction Sheet (non U.S.)

English