




Wire Protection & Management > Heat Shrink Molded Shapes > Heat Shrink Boots > Low Profile Heat Shrink Boots: Poly Molded, Lipped, Straight



Molded Part Shape: 180°

Molded Part Shape Code: 202

Lipped: Yes

Material Code: 4

Heat Shrink Boot Material Systems Code: 10

[All Low Profile Heat Shrink Boots: Poly Molded, Lipped, Straight \(223\)](#)

Features

Product Type Features

Molded Part Shape	180°
-------------------	------

Configuration Features

Lipped	Yes
--------	-----

Body Features

Material Code	4
Heat Shrink Boot Material Systems Code	10
Adhesive Pre-Coat	No
Material	Polyolefin Flexible Modified

Dimensions

Wire/Cable Outside Diameter	.787 in, .87 in, .9 in, .94 in, 1 in, 1.02 in, 1.1 in, 1.18 in, 1.26 in, 1.34 in, 20 mm, 22 mm, 24 mm, 26 mm, 28 mm, 30 mm, 32 mm, 34 mm
Cable Diameter Range	17.5 – 39.1 mm[.689 – 1.539 in]

Usage Conditions

Operating Temperature Range	-55 – 135 °C[-67 – 275 °F]
-----------------------------	----------------------------

Operation/Application

Power Cable Accessory	No
-----------------------	----



Industry Standards

Approved Standards	SAE AS I 81765/1, Type II, UL 224, File E85381
Government Qualified	No

Other

Molded Part Shape Code	202
Fluid/Chemical Resistance	Occasional exposure to fluids
Adhesive Options	/42 Precoat
Adhesive Type	Adhesive Purchased Separately

Product Compliance

For compliance documentation, visit the product page on TE.com>


EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2021 (211) Candidate List Declared Against: JAN 2021 (211) Does not contain REACH SVHC
Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts





TE Part # 890060-000
[S1017-1.0X50](#)




TE Part # CJ2087-000
[HL2010E-KIT-120V](#)


Customers Also Bought



TE Part #057837-000
Low Profile HS Boots: Blow Molded, Slim Line, Lipped, Straight



TE Part #095226-000
[S1030-TAPE-3/4X33FT](#)



TE Part #158631-000
[44AM1131-20-MST3-9CS2275](#)



TE Part #290139-000
Slim Line Heat Shrink Boots: Non Lipped, Straight



TE Part #3043434002
Single Wall NTFR: Heat Shrink Tubing, 1.75:1 Shrink Ratio




TE Part #YDTS26Z25-24PNV001
[D38999: Straight Plug, 25-24 Insert](#)



TE Part #2101580-2
[Sz 5 plug dust cap](#)



TE Part #036493-000
[202E346-51-0-CS5324](#)



TE Part #341925M017
[NTFR-1/4-0-SP-CS5445](#)

Documents

Product Drawings

[202D285-4-0](#)

English

Datasheets & Catalog Pages

[1654025_Sec4_4](#)

English

[Raychem Molded Parts Visual Guide](#)

English



Product Specifications

[Product Specification](#)

English

Product Environmental Compliance

[Safety Datasheet](#)

[Safety Datasheet](#)

German

[Safety Datasheet](#)

English

[Safety Datasheet](#)

[Safety Datasheet](#)

French

[Safety Datasheet](#)

[Safety Datasheet](#)

[Safety Datasheet](#)

[Safety Datasheet](#)