



Relays, Contactors & Switches > Contactors > Definite Purpose Contactors > DP CONTACTORS, 3 POLE, 20-40FLA



Pole Configuration: 3

Definite Purpose Contactor Coil Voltage Rating: 120 VAC

Definite Purpose Contactor Contact Current Rating: 25 A

Definite Purpose Contactor Mounting Type: Panel

Definite Purpose Contactor Contact Arrangement: 3 Form X, 3PST-NO-DM

[All DP CONTACTORS, 3 POLE, 20-40FLA \(43\)](#)

Features

Product Type Features

Molded	No
Product Category	Electromechanical Relays
Product Type	Contactor
Arc Cover	With
Product Classification	Relays - Contactors
Model	98
Contactor Type	Definite Purpose
Terminal Configuration	10-32 Screw, Quick Connect

Configuration Features

Auxiliary Switch Contact Arrangement	Without
--------------------------------------	---------

Electrical Characteristics

Actuating System	AC
Coil Voltage (Max)	120 VAC
Definite Purpose Contactor Coil Voltage Rating	120 VAC
Definite Purpose Contactor Coil Resistance	180 Ω
Definite Purpose Contactor Contact Switching Voltage (Max)	600 VAC

Contact Features



Contact Base Material	Silver Cadmium Oxide
Pole Configuration	3
Definite Purpose Contactor Contact Current Rating	25 A
Definite Purpose Contactor Contact Arrangement	3 Form X, 3PST-NO-DM

Termination Features

Coil Termination	Quick Connect
------------------	---------------

Mechanical Attachment

Mounting Plate	With
Definite Purpose Contactor Mounting Type	Panel

Dimensions

Wire Size	1.31 – 8.37 mm ²
-----------	-----------------------------

Industry Standards

UL Flammability Rating	UL 94V-0
Agency Approval	CSA Certified, UL Recognized

Packaging Features

Packaging Method	Loose Piece
------------------	-------------

Other

Comment	Stranding must be split for 8 AWG wire.
Torque	25 in-lbs

Product Compliance

For compliance documentation, visit the product page on [TE.com](#)>

EU RoHS Directive 2011/65/EU	Compliant with Exemptions
EU ELV Directive 2000/53/EC	Not Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2021 (211) Candidate List Declared Against: JAN 2021 (211) SVHC > Threshold: Cadmium oxide (10.81% in Component Part) Article Safe Usage Statements: Use personal protective equipment as required. Do not eat, drink or smoke when using this product. Recycle if possible and dispose of the article by following all applicable governmental regulations relevant to your geographic location.
Halogen Content	Not Yet Reviewed for halogen content



Solder Process Capability

Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # CAT-P592-R472A
PIDG RING TONGUE TERMINALS



TE Part # CAT-P592-SP118
PIDG SPADE TONGUE TERMINALS



TE Part # 175022-1
250 PL EX REC. 18-14AWG PTBR



TE Part # 1611434-8
98220-337=AUXILARY SPDT SWITCH

Also in the Series | Products Unlimited 3100



Definite Purpose Contactors(80)

Customers Also Bought



TE Part #282857-7
TERMI-BLOK PCB MOUNT 90 7P.5



TE Part #2-2176415-1
8W STD M/OX 5% 200R



TE Part #6609068-1
CORCOM AYA SERIES 3-PHASE FILTERS



TE Part #102972-1
01 MODII HDR SRST B/A .100CL



TE Part #1-530745-8
MINI BX RCPT ASSY 80P SEALED

TE Part #137845-000
ST18-3-9039

TE Part #YDTS26F25-29SAV001
D38999: Straight Plug, 25-29 Insert

TE Part #1423675-9
W57-XB7A4A10-15=CKTBKR,THERM,P

TE Part #1-1811927-4
8Q8 Size 25 Rcpt,A Key OD

TE Part #547647-000
MTC100-BJ1-P33

Documents

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_9-1611015-7_B.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_9-1611015-7_B.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_9-1611015-7_B.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

Model 98 - 3100 Definite Purpose Contactor 3-pole, 20-40 FLA AC Coil

English

Industrial Relays Quick Reference Guide

English

Industrial Relays Quick Reference Guide

Japanese

Industrial Relays Quick Reference Guide