



Application Tooling > Portable Crimp Tools



Tooling Type: **Reflector**

Features

Other

Tooling Type	Reflector
--------------	-----------

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2021 (211) Candidate List Declared Against: JUN 2020 (209) SVHC > Threshold: Not Yet Reviewed
Halogen Content	Not Yet Reviewed for halogen content
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # 582602-000  
[AA-400-32-MK3-SUPHTR-120V](#)

Customers Also Bought



TE Part #582602-000  
[AA-400-32-MK3-SUPHTR-120V](#)



TE Part #620040-000  
[D-108-07](#)




TE Part #208550-1  
[AMPLIMITE RECEPT ASY,COAX MIX](#)




TE Part #697123-000  
[MTC100-JB2-S14](#)



TE Part #YDTS24G25-35SNV001  
[Jam Nut Receptacle: D38999, Electroless Plating, 25-35 Insert](#)



TE Part #939462-000  
[D-602-1110](#)



TE Part #244913-000  
[DK-621-0035-2P](#)



TE Part #843532-000  
[101A062-4/42-0](#)



TE Part #979663-000  
[AA-400-102-MINI-SOLD-TIP](#)



TE Part #650083N002  
[D-436-59CS2612](#)

Documents

[Datasheets & Catalog Pages](#)  
[1654025\\_Sec10\\_AA-400](#)

English

[Raychem Application Tooling](#)

English

[Crimp Term Whitepaper-Use the Right Tool 1-1773953-1](#)

English

[CRIMPING WHERE FORM MEETS FUNCTION](#)



English

Product Specifications  
SOLDER SLEEVE REFLECTOR

English