AD-1319-9-HOLD-FIX-PACKAG ✔ ACTIVE

Raychem

TE Internal #: 993850-000

Portable Crimp Tools, Manual, Holder Assembly

View on TE.com >

Application Tooling > Portable Crimp Tools



TE Certification: **Cannot be Certified**

Power Technology Type: **Manual**

Tooling Type: **Holder Assembly**

Features

Other

TE Certification	Cannot be Certified
Power Technology Type	Manual
Tooling Type	Holder Assembly

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Out of Scope
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2021 (211) Candidate List Declared Against: JUN 2020 (209) SVHC > Threshold: Not Yet Reviewed
Halogen Content	Out of Scope - excluded from Halogen requirements
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits

as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: https://echa.europa.eu/guidance-documents/guidance-on-reach

Compatible Parts



TE Part # 993872-000
AT-1319-12

TE Part # 395241-000
AT-1319-22

Customers Also Bought




TE Part #46673
DAHT STRATO 22-16 ASSY




TE Part #354940-1
PRO-CRIMPER III FRAME W/O DIES



TE Part #47387
DAHT PG PIDG 20-14 ASSY



TE Part #165805-000
D-602-0144




TE Part #170342-1
250 FASTON,REC.,20-14 AWG,BR



TE Part #335276-000
TTVF COLOR CODING FLAGGING PVF LABELS



TE Part #323913
PIDG RING TONGUE TERMINALS



TE Part #46988
DAHT STRATO 16-14 ASSY

TE Part #ZPF000000000000921
057-0590-80

TE Part #395241-000
AT-1319-22

Documents

Product Drawings

AD-1319-9

English

AD-1319-9

English

Datasheets & Catalog Pages

Raychem Application Tooling

English

Crimp Term Whitepaper-Use the Right Tool 1-1773953-1

English

CRIMPING WHERE FORM MEETS FUNCTION

English

Product Specifications

INSTALLATION PROCEDURE USING AD-1319 HOLDING FIXTURE

English