

VERSAFLEX-3/8-0-SP ✓ ACTIVE

Raychem | Raychem VERSAFLEX


TE Internal #: CH02034001

Raychem VERSAFLEX, Heat Shrink Tubing, Black, Braid Wall Type, Polyester, Non-Flame-Retardant, Reel, Operating Temperature Range -50 – 150 °C

[View on TE.com >](#)



Heat Shrink Tubing



Primary Product Color: **Black**

Wall Type: **Braid**

Primary Product Material: **Polyester**

Heat Shrink Tubing Flammability: **Non-Flame-Retardant**

Packaging Method: **Reel**

Features

Product Type Features

| | |
|----------------|-----------|
| Product Family | VERSAFLEX |
| Wall Type | Braid |

Body Features

| | |
|--------------------------|-----------|
| Primary Product Color | Black |
| Primary Product Material | Polyester |
| Flexibility | Flexible |

Dimensions

| | |
|-------------------------------|-----------------------------|
| Heat Shrink Tubing Size Range | 4.7 – 16 mm[.185 – .629 in] |
|-------------------------------|-----------------------------|

Usage Conditions

| | |
|---------------------------------|---------------------|
| Fluid Resistance | Splash Protection |
| Heat Shrink Tubing Flammability | Non-Flame-Retardant |
| Operating Temperature Range | -50 – 150 °C |
| Heat Shrink Tubing Resistance | Mechanical Damage |

Product Availability

| | |
|-------------------|--------|
| Applicable Region | Global |
|-------------------|--------|

Packaging Features

| | |
|------------------|------|
| Packaging Method | Reel |
|------------------|------|



Other

| | |
|-----------------------------------|--------|
| Meets Low Outgassing Requirements | No |
| Product Source | Europe |

Product Compliance

For compliance documentation, visit the product page on TE.com>

| | |
|---|---|
| EU RoHS Directive 2011/65/EU | Compliant |
| EU ELV Directive 2000/53/EC | Compliant |
| China RoHS 2 Directive MIIT Order No 32, 2016 | No Restricted Materials Above Threshold |
| EU REACH Regulation (EC) No. 1907/2006 | Current ECHA Candidate List: JAN 2021 (211) Candidate List Declared Against: JAN 2021 (211) Does not contain REACH SVHC |
| Halogen Content | Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free |
| Solder Process Capability | Not applicable for solder process capability |

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # CJ2087-000
HL2010E-KIT-120V




TE Part # EG1114-000
CV1981-ST-230V1600W-EU

Also in the Series | Raychem VERSAFLEX



Heat Shrink Tubing(29)

Customers Also Bought



TE Part #146995-000
TXR40AB00-1410AI



TE Part #103648-2
03 MTE RCPT HSG SR RIB .100CL



TE Part #1719183-1
MQS, CONNECTOR HOUSING



TE Part #1-962917-2
TIMER, RECEPTACLE AND TAB




TE Part #1633988-2
CRIMPER, INSUL BOX PREMIUM



TE Part #CT56603001
55A1121-22-0/9-9CK0001




TE Part #1544980-1
TAB HOUSING, 8MM NG1 PLUS, 2 WAY



TE Part #154740-1
PIN .175 DIA REC 20-16AWG PB WAY



TE Part #1-2217206-3
Blade, Slug



TE Part #160666-5
110 FASTON,REC.,26-22 AWG,TPBR

Documents

Datasheets & Catalog Pages

[Application Tooling for Raychem Heat Shrink Product](#)

English

[VERSAFLEX - Expandable Braided Polyester Sleeving](#)

English

Product Specifications



Quality Specification

English