



ZHD-SCE

TE Internal #: EC9894-000

ZHD-SCE, Printable Tubing, Ladder Printable Tubing Type, Fluid Resistant & Low Fire Hazard Printable Tubing Grade, 2:1 Printable Tubing Shrink Ratio

[View on TE.com >](#)

Identification & Labeling > Printable Tubing > ZHD-SCE LFH & FLUID RESISTANT SLEEVES



Printable Tubing Type: **Ladder**

Printable Tubing Grade: **Fluid Resistant & Low Fire Hazard**

Printable Tubing Shrink Ratio: **2:1**

Primary Product Color: **White**

Markers per Sleeve: **1**

[All ZHD-SCE LFH & FLUID RESISTANT SLEEVES \(88\)](#)

Features

Product Type Features

Printable Tubing Type	Ladder
Printable Tubing Grade	Fluid Resistant & Low Fire Hazard

Body Features

Printable Tubing Shrink Ratio	2:1
Primary Product Color	White
Markers per Sleeve	1

Dimensions

Product Length	50 mm[2 in]
Supplied Inner Diameter	3.2 mm[.126 in]
Recovered Inside Diameter	1.5 mm[.06 in]
Compatible Cable Diameter Range	1.7 – 2.6 mm[.069 – .105 in]

Usage Conditions

Operating Temperature Range	-55 – 135 °C[-67 – 275 °F]
-----------------------------	----------------------------

Operation/Application

Recommended Ribbon	See TE Document 411-121005 the Printer Product Ribbon Matrix
--------------------	--

Printer/Label Features

Recommended Printer	See TE Document 411-121005 the Printer Product Ribbon Matrix
Printer Technology	Thermal Transfer

Packaging Features

Packaging Quantity	1000
--------------------	------

Product Compliance

For compliance documentation, visit the product page on [TE.com](#)>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2021 (211) Candidate List Declared Against: JAN 2021 (211) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # 1-2186500-1
T3212-PRINTER

TE Part # 1-2186502-1
T3224-PRINTER

TE Part # 1-2186503-1
T3224-SWARE-PRINTER

TE Part # CP8122-000
T6112DS-PRINTER

TE Part # 1-2186501-1
T3212-SWARE-PRINTER

Also in the Series

ZHD-SCE

Printable Tubing(88)

Customers Also Bought

TE Part #66504-9
D-Sub Conn Contacts: Socket, Phosphor Bronze, Signal, Size 20

TE Part #EC9900-000
ZHD-SCE LFH & FLUID RESISTANT SLEEVES

TE Part #206247P038
SCT-NO.4-E2-0-STK

TE Part #42281-1
FF 250 REC 18-14AWG BR

TE Part #5-1618387-7
LEV200A5NAF=RELAY, 24Vdc SPST NO

TE Part #1473672-1
TH/.025 CONNECTOR SYSTEM, HOUSING

TE Part #964274-2
TIMER, RECEPTACLE AND TAB

TE Part #794606-1
MICRO MNL RPT CNT STRIP 20-24



Documents

Product Drawings

ZHD-SCE-1K-3.2-50-9

English

Datasheets & Catalog Pages

TTDS for ZHD-SCE, LOW FIRE HAZARD, DIESEL RESISTANT

English

IDENTIFICATION SELECTION GUIDE

English

Product Specifications

Product Specification

English