



All PCB MOUNT POWER TRANSFORMERS (0)

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2021 (211) Candidate List Declared Against: JUN 2020 (209) SVHC > Threshold: Not Yet Reviewed
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>


Compatible Parts



TE Part # CAT-T3437-T1
T1K WHITE POLYIMIDE LABELS

Also in the Series


Customers Also Bought



TE Part #966066-3
ADERENDHUELSE N TK




TE Part #1546306-4
4P .374" DR BARRIER STRIP



TE Part #1-1393143-2
27E129=SOCKET,R10,16,PC,PHEN



TE Part #1-1879355-3
RR03 5% 13K AMMO



TE Part #966066-1
ADERENDHUELSE N BL



TE Part #1672326-6
PCB MOUNT POWER TRANSFORMERS

Documents

Product Drawings

4900-8012RE64=TRANSFORMER

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_1672326-2_C.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_1672326-2_C.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_1672326-2_C.3d_stp.zip



English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

Flyer - 4900 Series Power Transfomers for PC Board Mounting

English

Industrial Relays Quick Reference Guide

English

Industrial Relays Quick Reference Guide

Japanese

Industrial Relays Quick Reference Guide