



Connectors > Pluggable IO Connectors & Cages > SFP/SFP+/zSFP+ > SFP+ Stacked Cage Assemblies



Pluggable I/O Product Type: **Cage Assembly with Integrated Connector**
Data Rate (Max): **16 Gb/s**
EMI Containment Feature Type: **Elastomeric Gasket**
Pluggable I/O Applications: **SFP+**
Included Lightpipe: **Yes**

[All SFP+ Stacked Cage Assemblies \(122\)](#)

Features

Product Type Features

Form Factor	SFP+
Cage Type	Stacked
Pluggable I/O Product Type	Cage Assembly with Integrated Connector
Integrated Lightpipes	Yes
Connector System	Cable-to-Board
Sealable	Yes
Connector & Contact Terminates To	Printed Circuit Board

Configuration Features

Port Matrix Configuration	2 x 2
Lightpipe Configuration	Single Triangular (Outer)
Number of Ports	4
Number of Positions	80

Electrical Characteristics

Data Rate (Max)	16 Gb/s
-----------------	---------

Contact Features

Tail Plating Material	Tin
Contact Mating Area Plating Thickness	.76 µm



Contact Mating Area Plating Material	Gold or Gold Flash over Palladium Nickel
--------------------------------------	--

Termination Features

Termination Method to Printed Circuit Board	Through Hole - Press-Fit
---	--------------------------

Mechanical Attachment

PCB Mounting Style	Through Hole - Press-Fit
Connector Mounting Type	Board Mount

Housing Features

Cage Material	Nickel Silver
Centerline (Pitch)	.8 mm[.032 in]

Dimensions

Tail Length	3 mm[.118 in]
PCB Thickness (Recommended)	1.5 mm[.059 in]

Usage Conditions

Operating Temperature Range	-55 – 105 °C[-67 – 221 °F]
-----------------------------	----------------------------

Operation/Application

Heat Sink Compatible	No
Pluggable I/O Applications	SFP+
Circuit Application	Signal

Industry Standards

UL Flammability Rating	UL 94V-0
------------------------	----------

Packaging Features

Packaging Method	Box
------------------	-----

Other

EMI Containment Feature Type	Elastomeric Gasket
Included Lightpipe	Yes

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold



EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2021 (211) Candidate List Declared Against: JAN 2021 (211) Does not contain REACH SVHC
Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

 TE Part # CAT-C11-H50626 SFP+ to SFP+ I/O Cable Assembly: 30 AWG	 TE Part # CAT-C11-N490333 QSFP28-Four SFP+ Cable Assembly: 30 AWG	 TE Part # CAT-C11-N490325 QSFP28-Four SFP+ Cable Assembly: 26 AWG	 TE Part # CAT-C11-N49011142 SFP28 to SFP28 Cable Assembly: 32 AWG
 TE Part # CAT-C11-N4901114 SFP28 to SFP28 Cable Assembly: 30 AWG	 TE Part # CAT-C11-N49011 SFP28 to SFP28 Cable Assembly: 26 AWG	 TE Part # CAT-Q17-N49011 QSFP56-Four SFP56 Cable Assembly: 30 AWG	 TE Part # CAT-Q17-N490333 QSFP56-Four SFP56 Cable Assembly: 26 AWG




TE Part # CAT-C11-G28037
SFP56 to SFP56 Cable Assembly: 30 AWG



TE Part # CAT-C11-G28
SFP56 to SFP56 Cable Assembly: 26 AWG



TE Part # 4-2334985-2
SFP56 DIRECT ATTACH CA, 1M, 32AWG



TE Part # 1888901-1
SFP+ EMI Plug



TE Part # 1761394-1
DUST COVER, SFP, GANGED & STACKED




TE Part # CAT-C11-H5
SFP+ to SFP+ I/O Cable Assembly: 24 AWG




TE Part # CAT-C11-H506
SFP+ to SFP+ I/O Cable Assembly: 26 AWG



TE Part # CAT-C11-H5062
SFP+ to SFP+ I/O Cable Assembly: 28 AWG



TE Part # 2018280-2
KIT, SEATING TOOL, SFP+2x2



TE Part # 2063048-3
SFP, 2x2 EXTRACTION TOOL ASSY



TE Part # 2142970-1
CABLE ASSY, MICRO SFP+ TO STD SFP+, 0.5M



TE Part # 2142970-2
CABLE ASSY, MICRO SFP+ TO STD SFP+, 1M


Customers Also Bought



TE Part #5748440-2
D-Sub Receptacle Assy: Vertical, Action Pin, Shell Size 2, 2.74mm



TE Part #2170619-2
SFP accessories



TE Part #2170551-2
1X6 CAGE ASSEMBLY, BEHIND BEZEL, W/ SQR



TE Part #148296-2
064 EURO TYP R RECEPT EON ASSY



TE Part #2-1658046-1
MSB0.80PL11ASY040FL,F,TY



TE Part #2170507-5
1X3 QSFP CAGE ASSY



TE Part #2170551-1
1X6 CAGE ASSEMBLY, BEHIND BEZEL, W/ SQR



TE Part #5120747-1
Z-PACK HS3 HDR ASY 10R 50P



TE Part #5765271-1
WAVE CRIMP ACTION PIN HEADER ASSY



TE Part #7-1734857-4
PCI EXP STRADDLE 98P BLK 15u"

Documents

Product Drawings

SFP+assy 2x2 gasket Outer Lp Sn

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_2007417-7_F.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_2007417-7_F.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_2007417-7_F.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

1773408-1 Pluggable Input/Output Solutions catalog - SFP+ section

English

SFP+ Product Family: Cages, Connectors, Cable Assemblies 4-1773449-5

English

4-1773455-3 - Quick Reference Guide SFP+ Solutions

English

Product Specifications

Application Specification

English

Product Environmental Compliance

TE Material Declaration

English

Instruction Sheets

Instruction Sheet (U.S.)



English

[Instruction Sheet \(U.S.\)](#)

English