

2040727-1 x OBSOLETE

DDR3 DIMM, DDR3 SO DIMM

TE Internal #: 2040727-1

TE Internal Description: DDR3 DIMM ASSY

[View on TE.com >](#)



Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2021 (211) Candidate List Declared Against: JUL 2019 (201) SVHC > Threshold: Not Yet Reviewed
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Reflow solder capable to 260°C

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Also in the Series | [DDR3 DIMM](#)



DIMM Sockets(14)

Also in the Series | DDR3 SO DIMM



DIMM Sockets(9)



SO DIMM Sockets(3)

Customers Also Bought



TE Part #2118721-4
STD SHIELD COVER, AL-38.60X25.
90X2.00MM



TE Part #413194-1
BNC RF Connector: Male (Jack), Right-
angle, 75 Ohm



TE Part #2289129-3
ZQSFP+ CAGE& CONN 2X2, EMI
SPRING, 4 LP



TE Part #5748989-1
D-Sub Receptacle Assembly: Right
Angle, Shell Size 3, 2.77mm



TE Part #1-5353727-0
.6FHP08H,280,B,GIG,08/Sn,ST,NSYes



TE Part #1-5353729-0
.6FHR04H,280,B,GIG,08/Sn,ST,NSYes



TE Part #2085958-1
ICCON,SIZE 4,LOCKING PIN
ASSEMBLY



TE Part #5767025-1
MICTOR .707 PLUG ASSY, 38 POS.



TE Part #NB19382001
RNF-100-1/8-YO-STK



TE Part #5-2287906-1
FAKRA, 1 POS, EDGE MOUNT, 12
OCLOCK ASSY



Documents

Product Drawings

[DDR3 DIMM ASSY](#)

English

CAD Files

[3D PDF](#)

3D

Customer View Model

[ENG_CVM_CVM_2040727-1_F.2d_dxf.zip](#)

English

Customer View Model

[ENG_CVM_CVM_2040727-1_F.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_2040727-1_F.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

[DDR3 DIMM Sockets Flyer 6-1773454-7 05/09](#)

English

[6-1773457-3_DDR3_DIMM_SOCKETS](#)

Product Environmental Compliance

[TE Material Declaration](#)

English